



- Manual indexing button, smooth body , no flange
- Two versions available.
- Material :
 - Body: Stainless steel 303
 - Pin: Hardened stainless steel 420
 - Head: Dark grey thermosetting plastic

Info.

- Index bolts are used where lateral movement is required to be blocked. Pulling the handle releases the pin. With the M version, the pin can be held in the retained position.
- Bolts should be welded using a WIG inert gas process



DISCOUNTS

Qty.	1+	6+	20+
Disc.	List -10% On request		

Part number	ØD	ØD1	ØD2	L	L1	H	Fx30°	Spring force		Price each 1 to 5
								Initial (N)	Final (N)	
SLBW10-L/SS	4	10	18	38,5	21	4	1,0	6	12	12,62 €
SLBW10-M/SS	4	10	18	38,5	21	4	1,0	6	12	15,86 €
SLBW12-L/SS	5	12	21	43,5	24	5	1,3	5	12	11,78 €
SLBW12-M/SS	5	12	21	43,5	24	5	1,3	5	12	15,10 €
SLBW14-L/SS	6	14	25	51,7	28	6	1,8	6	14	13,41 €
SLBW14-M/SS	6	14	25	51,7	28	6	1,8	6	14	17,22 €
SLBW18-L/SS	8	18	33	68,0	36	8	2,3	15	35	17,81 €
SLBW18-M/SS	8	18	33	68,0	36	8	2,3	15	35	21,03 €
SLBW22-L/SS	10	22	33	74,0	40	10	2,8	15	40	28,17 €
SLBW22-M/SS	10	22	33	74,0	40	10	2,8	15	40	33,07 €

Altri prodotti...



CQA30
Slitta di regolazione
miniatura, 30



S_2RS
Cuscinetto radiale a
sfere, Inox



PTA100
Piede snodato con
base stampata Ø100,
15000N



PSG085
Ingranaggio dritto di
precisione, Inox 316



AT5P_AT10P
Piastra di giunzione
per cinghia AT, AT10



GLB
Piccolo volano a 6
alette, Tecnopolimero
- Ottone




DIV_SS
Pistoncino a molla,
Bloccabile - Inox




P45
Riduttore a ruota e
vite senza fine, fino a
40 Nm



SSB
Ingranaggio conico
inox, 1:1



PRF45_GOU
Canalina, Accessori



QNUP
Cuscinetto a singola
corona di rulli
cilindrici, Anello



PR105
Piede fissabile con
snodo - poliammide, Ø
103

Prodotti correlati



SLBW
Pistoncino a molla, Da
saldare - Acciaio



BIMSS
Pistoncino a molla,
Miniatura inox