Pull to release


SLBWss

- ***Manual indexing button, smooth body , no flange***
- *Two versions available.*
- *Material :*
  Body: Stainless steel 303
  Pin: Hardened stainless steel 420
  Head: Dark grey thermosetting plastic




Info.

- *Index bolts are used where lateral movement is required to be blocked. Pulling the handle releases the pin. With the M version, the pin can be held in the retained position.*
- *Bolts should be welded using a WIG inert gas process*



"L" type without retaining mechanism



"M" type with retaining mechanism

DISCOUNTS

Qty.	1+	6+	20+
Disc.	List	-10%	On request

Part number	ØD	ØD1	ØD2	L	L1	H	Fx30°	Spring force Initial (N)	Spring force Final (N)	Price each 1 to 5
SLBW10-L/SS	4	10	18	38,5	21	4	1,0	6	12	12,62 €
SLBW10-M/SS	4	10	18	38,5	21	4	1,0	6	12	15,86 €
SLBW12-L/SS	5	12	21	43,5	24	5	1,3	5	12	11,78 €
SLBW12-M/SS	5	12	21	43,5	24	5	1,3	5	12	15,10 €
SLBW14-L/SS	6	14	25	51,7	28	6	1,8	6	14	13,41 €
SLBW14-M/SS	6	14	25	51,7	28	6	1,8	6	14	17,22 €
SLBW18-L/SS	8	18	33	68,0	36	8	2,3	15	35	17,81 €
SLBW18-M/SS	8	18	33	68,0	36	8	2,3	15	35	21,03 €
SLBW22-L/SS	10	22	33	74,0	40	10	2,8	15	40	28,17 €
SLBW22-M/SS	10	22	33	74,0	40	10	2,8	15	40	33,07 €

Altri prodotti...


GG2

Ingranaggio dritto rettificato, Acciaio trattato


PTA100

Piede snodato con base stampata Ø100, 15000N


GEC

Chiusura a leva in gomma con aggancio, Bloccabile


YG4

Ingranaggio dritto PRESTAZIONE, Acciaio 35NCD6


PW_PWG25

Ruota di precisione, Bronzo


CHM40-MOT

Motoriduttore AC asincrono da 0,18 a 0,55kW, 0.18 a 0.55kW


PPD

Pistoncino a molla, Per lamiera


BSPT

Morsetto per guide, Rondo


E50

Riduttore a rinvio angolare, da 3 a 41 Nm


NK40

Guida mini Drylin® N, Larghezza 40 mm


PM4

Vite senza fine, Acciaio non temprato


BPHF

Sfera portante a incastro con flangia, Forte

Prodotti correlati


SLBW

Pistoncino a molla, Da saldare - Acciaio


BIMSS

Pistoncino a molla, Miniatura inox