



- Manual indexing button, smooth body , no flange
- Two versions available.
- Material :
  - Body: Stainless steel 303
  - Pin: Hardened stainless steel 420
  - Head: Dark grey thermosetting plastic

### Info.

- Index bolts are used where lateral movement is required to be blocked. Pulling the handle releases the pin. With the M version, the pin can be held in the retained position.
- Bolts should be welded using a WIG inert gas process



### DISCOUNTS

Qty.	1+	6+	20+
Disc.	List -10% On request		

Part number	ØD	ØD1	ØD2	L	L1	H	Fx30°	Spring force		Price each 1 to 5
								Initial (N)	Final (N)	
SLBW10-L/SS	4	10	18	38,5	21	4	1,0	6	12	12,62 €
SLBW10-M/SS	4	10	18	38,5	21	4	1,0	6	12	15,86 €
SLBW12-L/SS	5	12	21	43,5	24	5	1,3	5	12	11,78 €
SLBW12-M/SS	5	12	21	43,5	24	5	1,3	5	12	15,10 €
SLBW14-L/SS	6	14	25	51,7	28	6	1,8	6	14	13,41 €
SLBW14-M/SS	6	14	25	51,7	28	6	1,8	6	14	17,22 €
SLBW18-L/SS	8	18	33	68,0	36	8	2,3	15	35	17,81 €
SLBW18-M/SS	8	18	33	68,0	36	8	2,3	15	35	21,03 €
SLBW22-L/SS	10	22	33	74,0	40	10	2,8	15	40	28,17 €
SLBW22-M/SS	10	22	33	74,0	40	10	2,8	15	40	33,07 €

## Altri prodotti...



PAMF80EB  
Piede snodato con base stampata fissabile Ø80, Piede snodato



HCSS  
Grano con punta a coppa, punta a coppa



SLB  
Pistoncino a molla, acciaio classe 5.8



GB-RA  
Ingranaggio dritto ottone, Ottone CuZn39Pb3



LVT  
Mini martinetto motorizzato 4A, 4 ampere



HTD8M\_20  
Puleggia dentata di trasmissione tipo HTD, HTD8 Acciaio



ACL-PL  
Elementi di giunzione, Piastra di fissaggio - 176x86 mm



HTD8M\_50  
Puleggia dentata di trasmissione tipo HTD, HTD8 Acciaio



PTA50  
Piede snodato con base stampata Ø50, 4000N



E15  
Riduttore a rinvio angolare, da 0.40 a 2.53 Nm



GE\_ES\_2RS  
Snodo sferico, acciaio/acciaio e guarnizioni di tenuta



MCL  
Manicotto cilindrico maschiato, Cilindrico - inox

## Prodotti correlati



SLBW  
Pistoncino a molla, Da saldare - Acciaio



BIMSS  
Pistoncino a molla, Miniatura inox