


# TBE10


## Max carried payload 1kg

- Leadscrew table for manual use
- Right hand trapezoidal leadscrew TR10x2
- Guided by 2 shaft in steel on 4 brass bearings
- Axial accuracy < 0,20mm
- With clamping wingnut and grip knob
- Materials:  
Anodised aluminium and steel
- Working T° : from +5°C to +80°C






### Accessories

- Base plate with ruler TBE-BASE



### Admissible payload



	Static	Dynamic
Fmax (daN)	10	2,5
Cmax (Nm)	4	1
Mmax (Nm)	5	1

(40mm < r < 100mm)

### DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-10%	On request

Part number	Stroke (mm)	Max carried payload (kg)	Weight (kg)	Stock*	Price each
TBE10-50	50	1	0,51	-	241,34 €
TBE10-100	100	1	0,59	-	243,73 €

\*Depending on availability - Dimensions in mm




# Economic Mini-table with trapezoidal leadscrew

## Max carried payload 2kg


## TBE12

- Leadscrew table for manual use
- Right hand trapezoidal leadscrew TR10x2
- Guided by 2 shaft in steel on 4 brass bearings
- Axial accuracy < 0,20mm
- With clamping wingnut and grip knob
- Materials:  
Anodised aluminium and steel
- Working T° : from +5°C to +80°C




### Accessories


- Base plate with ruler **TBE-BASE**



### Admissible payload



$$C = P(N) \times r(m)$$



	Static	Dynamic
Fmax (daN)	20	5
Cmax (Nm)	8	2
Mmax (Nm)	10	2

(50mm < r < 150mm)

### DISCOUNTS

Qty	1+	2+	3+
Disc.	List -10%	On request	On request


Part number	Stroke (mm)	Max carried payload (kg)	Weight (kg)	Stock*	Price each
TBE12-50	50	2	0,91	-	272,82 €
TBE12-100	100	2	1,02	-	275,79 €
TBE12-150	150	2	1,13	-	278,77 €
TBE12-200	200	2	1,24	-	281,75 €

\*Depending on availability - Dimensions in mm

# TBE16


## Max carried payload 5kg

- Leadscrew table for manual use
- Right hand trapezoidal leadscrew TR12x3
- Guided by 2 shaft in steel on 4 brass bearings
- Axial accuracy < 0,20mm
- With clamping wingnut and grip knob
- Materials:  
Anodised aluminium and steel
- Working T° : from +5°C to +80°C




### Accessories


- Base plate with ruler TBE-BASE



### Admissible payload



$$C = P_{(N)} \times r_{(m)}$$



	Static	Dynamic
F <sub>max</sub> (daN)	40	12
C <sub>max</sub> (Nm)	17	4
M <sub>max</sub> (Nm)	20	5

(60mm < r < 200mm)

### DISCOUNTS

Qty	1+	2+	3+
Disc.	List -10%	On request	

Part number	Stroke (mm)	Max carried payload (kg)	Weight (kg)	Stock*	Price each
TBE16-50	50	5	1,53	-	300,14 €
TBE16-100	100	5	1,71	-	303,71 €
TBE16-150	150	5	1,89	-	307,27 €
TBE16-200	200	5	2,07	-	310,83 €

\*Depending on availability - Dimensions in mm





# Base plate for **economic** mini-table


## Allows X-Y cross tables

## TBEBASE


- **Base plate with ruler**
- To be screwed under the end supports
- Allows mounting in XY cross tables thanks to counterbored holes
- Ruler with graduation in mm
- Delivered with 8 fixing screws
- Material:
  - Plate Anodised aluminium
  - Stainless steel ruler
  - Zinc plated fixing screws



Simple assembly



Cross tables assembly



### DISCOUNTS

Qty	1+	2+	3+
Disc.	List -10%	On request	

Part number	For table	Stroke (mm)	C	HB	LB	E0	E1	F	ØD1	ØD2	P2	Weight (kg)	Stock <sup>1</sup>	Price each
TBE10-50/BASE	TBE10	50	69	9,0	110	26	59	12	5,2	9	5,0	0,20	-	54,92 €
TBE10-100/BASE	TBE10	100	69	9,0	160	26	59	12	5,2	9	5,0	0,28	-	62,29 €
TBE12-50/BASE	TBE12	50	83	9,5	132	46	73	12	6,5	11	6,5	0,30	-	74,69 €
TBE12-100/BASE	TBE12	100	83	9,5	182	46	73	12	6,5	11	6,5	0,40	-	80,64 €
TBE12-150/BASE	TBE12	150	83	9,5	232	46	73	12	6,5	11	6,5	0,50	-	86,82 €
TBE12-200/BASE	TBE12	200	83	9,5	282	46	73	12	6,5	11	6,5	0,60	-	92,92 €
TBE16-50/BASE	TBE16	50	98	11,5	150	58	88	16	6,5	11	6,5	0,47	-	82,30 €
TBE16-100/BASE	TBE16	100	98	11,5	200	58	88	16	6,5	11	6,5	0,62	-	90,79 €
TBE16-150/BASE	TBE16	150	98	11,5	250	58	88	16	6,5	11	6,5	0,77	-	99,16 €
TBE16-200/BASE	TBE16	200	98	11,5	300	58	88	16	6,5	11	6,5	0,92	-	107,48 €

<sup>1</sup> Depending on availability - Dimensions in mm

## Altri prodotti...




PSG125S  
Ingranaggio dritto di precisione, Inox 303



HRV  
Sistema di guida su binario a V Simple Select®, Binario con carrello



VTAP  
Vite a testa magnetica, Con rivestimento in gomma



CHB  
Riduttore a ruota e vite senza fine, fino a 73 Nm



CM\_CO  
Attrezzi Hygienic Usit® and Hygienic Design®, Protective inserts f...



CHA1056-UPA  
Cerniera su facciata in poliammide, Poliammide nera



FBL6000\_K13  
Spazzola al metro, Polipropilene nero striato (PP)



PGMT  
Maniglia a ponte a fissaggio anteriore, Innox



PLM-C  
Magnete piatto di fermo, Magnete di



PSG08  
Ingranaggio dritto di precisione, Acciaio



ETGamme  
Molla di trazione DIN2097, DIN 2097



BIMSS  
Pistoncino a molla, Miniatura inox

## Prodotti correlati




TBEbase10  
Economic mini-table with trapezoidal leadscrew, 1kg



TBEbase  
Base plate for economic mini-table, Allows X-Y cross tables



TBE16  
Economic mini-table with trapezoidal leadscrew, 5kg



TBL  
Mini tavola di posizionamento a vite metrica, 1kg