Fixed castor for aluminium profile

For loads up to 120kg

TPEF

- ***Castor for aluminium profil 40/45mm such as PRF4545***
- *Materials:*
  Plate: powder-coated steel sheet, natural aluminium colour
  Wheel: grey polypropylene (RAL 7001)



Advantages


- *Silent*
- *Will not mark floor*
- *Low rolling resistance*

Info

- *Fixing screws not supplied (See **PRF-ECL-M8** and **BHC8/CHC8 screws**)*



Typical application



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	H	Maximum load (N)	Weight (g)	Price each 1 to 9
TPE80/F	80	111	1000	484	22,14 €
TPE100/F	100	136	1100	577	26,60 €
TPE125/F	125	161	1200	675	29,80 €

Dimensions in mm

Altri prodotti...



TS01_TW01

Guida lineare su binario Drylin® T, fino al 7000 N



T5P_T10P

Piastra di giunzione per cinghia T, T10



MDB_MTB

Ingranaggio conico in plastica stampata , 2:1



HAS

Rondella girevole, Vite con spalla a testa piatta con intaglio




AT5P_AT10P

Piastra di giunzione per cinghia AT, AT5



AC

Piastrina di riscontro, 12,13,18 e 20mm



STL

Guida con spazzola, Spazzola



NSP

Morsetto base a 90°, Montaggio e regolazione rapidi



T5-10ECO

Puleggia dentata di posizionamento tipo



RCC_RCX

Rondella sferica - DIN6319, convessa



MAX22

Motoriduttore DC 12V e 24V DC, da 0,07 a



RDCss

Tenditore, Inox

Prodotti correlati



TPEpbd

Ruota per profili alluminio, Girevole con freno



PRF4545

Profilato alluminio standard, 45 x 45 mm



PRF_ECL_

Fissaggio, Dado quadrato con linguetta - Acciaio



BHC

Vite a testa bombata BHC , Inox A2