Swivel castor for aluminium profile

TPEPDB

For loads up to 120kg

- ***Swivel castor with brake for use with aluminium profile 40/45mm such as PRF4545***
- *Material:*
  Plate: powder-coated steel sheet, natural aluminium colour
  Wheel: grey polypropylene (RAL 7001)



Advantages


- *Silent*
- *Will not mark floor*
- *Low rolling resistance*

Info

- *Fixing screws not supplied*
(*See* **PRF-ECL-M8** *and* **BHC8/CHC8** *screws*)



Typical application



REMISES

Qté	1+	10+	30+
Rem.	Prix	-5%	Sur demande

Part number	ØD	H	Maximum load (N)	Weight (g)	Price each 1 to 9
TPE80/PDB	80	111	1000	710	32.11 €
TPE100/PDB	100	136	1100	787	35.05 €
TPE125/PDB	125	161	1200	873	37.15 €

Dimensions in mm

0 825 88 5000
Service 0,15 € / min + prix appel

Altri prodotti...


BLHT40

Rinvio angolare a T, da 4 a 10.30 Nm


BPTR

Tappo per tubo tondo, Standard


PDM_PDV

Detectable plastic palm grip, by metal detectors


RPP3

Cinghia di trasmissione RPP, RPP3


IN0

Ingranaggio interno, Acciaio 20NCD2


GARDLL

Bussola portamaschi, Acciaio o InoxInox


PDR-RD

Piede con ruota integrata, Ruota disassata


NCT

Giunto di collegamento, Ad angolo fisso


Q6

Cuscinetto radiale a sfere, Acciaio


INS100

Inserto auto-maschiante a passo


CPAS-H

Squadra pieghevole, Per carico pesante


CHA1056_U20

Cerniera ad avvitare, Sezione 90X60

Prodotti correlati


TPEf

Ruota per profili alluminio, Fissa


PRF4545

Profilato alluminio standard, 45 x 45 mm


PRF_ECL

Fissaggio, Dado quadrato con linguetta - Acciaio


CHC

Vite a testa cava esagonale CHC, Acciaio classe 12.19