
- ***Structural tube***
- *Materials: Stainless steel or anodised aluminium*
- *Square tube 25 x 25mm*



Accessories

- *Connectors* **NCT**
- *Caps* **BTC**
- *Slide profiles* **PGT**
- *Support profiles* **PSP**



DISCOUNTS

Qty.	1+	10+	21+
Disc.	List	-5%	On request

Part number	Material	H	W	Length (mm)	Weight (kg/m)	Stock*	Price each 1 to 9
TUBE25-25/SS	Stainless steel	25	25	3000	3,21	✔	70,08 €
TUBE25-25/AL	Aluminium	25	25	3000	1,09	✔	48,20 €

**Depending on availability - Dimensions in mm*

Altri prodotti...



PSG15

Ingranaggio dritto di precisione, Acciaio 20NCD2 cementato temprato



CDP

Boccola di posizionamento, Acciaio



CHMR63

Riduttore a ruota e vite senza fine, fino a 196 Nm



LVTMFC

Device for controlling limit switches, For mini-actuator LVT



BLHT60

Rinvio angolare a T, da 26 a 70 Nm



IN2

Ingranaggio interno, Acciaio 20NCD2



BAGSS

Anello di bloccaggio inox, Inox



T39_T49

Molla di trazione al metro inox, al metro



CHAR

Cerniera a molla, avvitabile



PSPD40

Manopola a pressione, PVC nero



PDM_PDV


, by metal detectors



PSG3S

Ingranaggio dritto di precisione, Inox 303

Prodotti correlati



BTC

Tappo per tubo quadrato, Standard



NCT_AT

Giunto di collegamento, Ad angolo variabile



NCT

Giunto di collegamento, Ad angolo fisso



NCT

Giunto di collegamento, Ad angolo fisso