

# H Type guide unit







UGH16 For  $\text{Ø}12 + \text{Ø}16$  actuators (ISO 6432)

- Guide system for actuator
- Fitted with 4 smooth bronze bearings
- Slides protected by wiper joints
- Actuator coupling available on front face
- Supplied with fixing screw for actuator
- Maintenance free
- Working temperature: +5 to +80 °C
- Maximum speed: 1 m/s
- Maximum loads: See end of section
- Material:

Body + face plate:  
anodised aluminium  
Couplings + screws:  
Zinc plated steel  
Guide shafts:  
Chromed steel

Excellent price/  
Quality ratio

Accurate even over  
long strokes



## DISCOUNTS

Qty	1+	6+
Disc.	List	On request

Part number	Stroke	Ø Actuator	Ø Guide rod	Weight (kg)	Price each 1 to 5
UGH16-25	25	12 and 16	10	0,43	212,86 €
UGH16-50	50	12 and 16	10	0,46	213,96 €
UGH16-100	100	12 and 16	10	0,52	216,20 €
UGH16-160	160	12 and 16	10	0,59	218,82 €
UGH16-200	200	12 and 16	10	0,64	220,61 €
UGH16-250	250	12 and 16	10	0,70	222,86 €

Dimensions in mm

## Altri prodotti...



SH0

Ingranaggio elicoidale ad assi paralleli , Acciaio 20NCD2



KKP-AR

Manicotto a sfere inclinate, Carichi elevati / -20° +200°



RBG

Ruota, Rivestimento in gomma - nucleo in polipropilene



NSU

Supporto per sensore, Morsetto universale base a 90°



DIV

Pistoncino a molla, Bloccabile - Acciaio



BCM\_HPBT

Spazzola cilindrica modulare, Filo poliestere PBT



CHV

Motovariatore meccanico, da 0,18 a 1,5kW



CHMR90

Riduttore a ruota e vite senza fine, fino a 540 Nm



CLAT

Maniglia a ripresa Hygienic Usit®, Inox



YG2

Ingranaggio dritto PRESTAZIONE, Acciaio



DOMI50

Accessori di collegamento, Piatto



PM4

Coppia ruota e vite senza fine, Bronzo

**Prodotti correlati**