



Small 6 lobe threaded handle

Black Duroplast bored insert

VBFP


- Operating element
- Materials:
Black phenolic Duraplast
Insert; brass or stainless steel

Advantages


- Easy grip
- Temperature resistant
- Good chemical resistance
- Easier to clean than technopolymer
- In machining applications, less likely to retain swarf

Good resistance

brass or stainless steel insert



VBFP20-VBFP30-VBFP/SS



VBFP40 to VBFP70

DISCOUNTS

Qty	1+	10+	20+	50+	100+	200+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	ØA	ØB	C	ØD	E	F	G	ØD1	Weight Price each	
									(g)	1 to 9
Brass insert										
VBFP20-M4	20	13	15	M4	11	7	8	7,5	6	4,00 €
VBFP20-M5	20	13	15	M5	11	7	8	7,5	7	4,14 €
VBFP20-M6	20	13	15	M6	11	7	8	7,5	10	4,21 €
VBFP30-M6	30	17	24	M6	15	11	12,5	9	16	4,83 €
VBFP30-M8	30	17	24	M8	15	11	12,5	9	17	5,08 €
VBFP40-M8	40	21	28	M8	18	13	15	11	29	5,87 €
VBFP40-M10	40	21	28	M10	18	13	15	11	31	5,91 €
VBFP50-M8	50	25	33	M8	18	15	18	13	43	7,31 €
VBFP50-M10	50	25	33	M10	18	15	18	13	45	7,39 €
VBFP50-M12	50	25	33	M12	18	15	18	13	47	7,39 €
VBFP60-M12	60	28	35	M12	25	15	20	13	70	9,23 €
VBFP70-M12	70	32	42	M12	25	21	21	13	96	11,21 €
VBFP70-M14	70	32	42	M14	25	21	21	15	94	11,21 €
VBFP70-M16	70	32	42	M16	25	21	21	17	93	12,40 €
Stainless steel insert										
VBFP20-M6/SS	20	13	15	M6	11	7	8	7,5	10	9,19 €
VBFP30-M6/SS	30	17	24	M6	15	11	12,5	9	16	9,81 €
VBFP40-M8/SS	40	21	28	M8	18	13	15	11	34	10,99 €
VBFP50-M8/SS	50	25	33	M8	18	15	18	13	49	11,90 €
VBFP50-M10/SS	50	25	33	M10	18	15	18	13	52	12,50 €

Dimensions in mm

Altri prodotti...



CMM
Testa a snodo
maschio DIN
ISO12240-4, Acciaio /
bronzo



BPHT
Sfera portante
fissaggio con perno
filettato, Forte



RJA11_27
Guarnizione in
gomma, Diverso
dall'aggancio



ATZY
Antivibrante elastico
sgolato, Acciaio



SLB
Pistoncino a molla,
acciaio classe 5.8



TSM T10M
Cinghia aperta al
metro tipo T, T5
Poliuretano armatura
in acciaio



BSM
Pressore a molla con
esagono incassato,
corpo e spina inox
303



IBJ
Snodo angolare a
180°, Acciaio



B_ECO
Ingranaggio conico -
Acciaio C43 - ECO, 1:1



VDS
Bloccaggio scorrevole
per la regolazione,



PF40NM
Riduttore a ruota e
vite senza fine, fino a



FBL6000_K19
Spazzola al metro,
Crine di cavallo nero

Prodotti correlati



VB
Volantino a 6 lobi,
Duroplast - Inox



GLB
Piccolo volano a 6
alette, Tecnopolimero
- Inox