


Threaded lifting ring

WBGv  RUD® Base rotates through 360°

- Lifting ring for loads liable to swivel or tilt.
- Mounted on ball bearings
- Can be rotated under load
- Easy installation, only a tapped hole required
- Heavy duty lifting ring, manufactured and tested to DIN EN1677-4
- Surface finish: Pink epoxy powder over zinc plating
- Thread is 100% electromagnetically tested for cracks, CORRUD-DT coated
- Pivots through 180°





Option


- Can be supplied with a longer thread and a mounting screw for use with a through hole or for mounting on lighter metals such as aluminium

Info


- Conforms to EU Directive 98/37/CE




Nominal SWL
Worst case lift
direction



Aligned by
hand, SWL
increases



Vertical load
SWL values doubled



Option:
Extended thread,
washer and nut




DISCOUNTS

Qty	1+	5+	10+	15+
Disc.	List -3%	-6%	On request	

Part number	Load CMU(t)			ØM	A	B	C	D	E	F	F max.	G	SW	Weight (kg)	Price each
	X	Y	Z												
WBG-V-M8	0,3	0,4	0,6	M8	8	31	29	30	76	13	102	36	27	0,18	102,28 €
WBG-V-M10	0,45	0,6	0,9	M10	8	31	29	33,5	78	17	122	38	30	0,29	108,02 €
WBG-V-M12	0,6	0,75	1,2	M12	10	49	35	42	107	21	140	47	36	0,41	114,79 €
WBG-V-M16	1,3	1,5	2,6	M16	13	46	38	48	114	25	180	56	41	0,59	123,10 €
WBG-V-M20	2	2,5	4	M20	13	54	35	62	137	33	223	67	55	1,42	206,79 €
WBG-V-M24	3,5	4,0	7	M24	18	66	40	81	173	40	255	88	70	2,63	277,98 €
WBG-V-M30	5	6,0	10	M30	22	90	50	99	221	50	330	106	85	5,09	370,98 €

*Depending on availability - Dimensions in mm

Our other products




PO

Pull handle - Multi-sector, Smooth hole



BFA

Shaft locking washer, E clip



CFC

Spring loaded position switch, Electric contact



CHMR75

Worm and wheel gear reducer, up to 298 Nm



LRX

Linear roller slide, Rail - from 9410 N to 101000 N



GRP2-14-A

Spring pin ISO8740, splined ISO 8740



AC156-157

Strike for toggle latch, 25.5mm



PRF_FIX_STD

Fastener for aluminium profile, Standard fastener



BH02

Single housed bearing assembly, Bearing



YG2

HEAVY DUTY spur gear, Steel 35NCD6



AT10-50ECO

AT type timing pulley, Economy range -



ZDB

Machined plastic bevel gear, 2:1

Complementary products



VRSSs

Male swivelling lifting rings stainless steel, Male swivelling - ...



VRM

Female swivelling lifting rings, Female swivelling



PPS

Lifting ring, Universal threaded



VLBG

Lifting ring, Rotating

Altri prodotti...



PTA100
Piede snodato con base stampata Ø100, Ø 100



PSG25
Ingranaggio dritto di precisione, Acciaio 35NCD6 pretrattato



H1
Ingranaggio elicoidale ad assi incrociati a 90°, Acciaio 20NCD2



INS100
Inserto auto-maschiante a passo grosso, Filetto largo



ERF
Terminale rapido per cavi, Terminale filettato




EHD08-3
Riduttore coassiale, da 20 a 50 Nm




FHCSS
Vite a testa svasata piana, Inox A2 - DIN 7991



PR85
Piede fissabile con snodo - poliammide, Ø 83



RPC
Ruota, Poliammide



CFC
Pressore a molla con esagono incassato, A contatto elettrico



BCM_TP
Spazzola cilindrica modulare, Filo in tampico



GMK17_BROSSE
Spazzola, Per imbottigliamento e imballaggio

Prodotti correlati



VRSSs
Anello di sollevamento, Orientabile maschio inox



VRM
Anello di sollevamento, Orientabile femmina



PPS
Anello di sollevamento, Gancio universale ad avvitare



VLBG
Anello di sollevamento, Girevole