
Digital position indicator


OP9

5 digit display

- ***5 digit display (99999) with red digits for tenths/ hundredths***
- *Shaft driven position indicator*
- *Displays linear or angular movement by use of mechanism driven by a rotating shaft*
- *Nonflammable polycarbonate case Protection IP54. Max. temperature 80°C*
- *Colour: orange*
- *Height of digits: 7mm, with 9mm lens*
- *Standard bore for shaft 30H7, smaller bores will require use of reducing sleeve*









Options

- Version with stainless steel parts available

Assembly

- Insert the indicator on to the shaft ensuring that the torque pin is inserted into the 6mm hole that should have been drilled previously. Reset the display to zero and secure the fixing screw.


View A


View B

DISCOUNTS

Qty.	1+	5+	10+	15+	25+
Disc.	List	-6%	-12%	-20%	On request

Part number	View	Pitch (mm)	Display after one turn (mm)	Max. speed (rpm)	Counting direction	Price each 1 to 4
OP9-A10-DX	A	1	001 0	300	clockwise	154,78 €
OP9-A30-DX	A	3	003 0	300	clockwise	154,78 €
OP9-A40-DX	A	4	004 0	200	clockwise	154,78 €
OP9-A50-DX	A	5	005 0	200	clockwise	154,78 €
OP9-A100-DX	A	10	010 0	100	clockwise	154,78 €
OP9-B10-DX	B	1	001 0	300	clockwise	154,78 €
OP9-B30-DX	B	3	003 0	300	clockwise	154,78 €
OP9-B40-DX	B	4	004 0	200	clockwise	154,78 €
OP9-B50-DX	B	5	005 0	200	clockwise	154,78 €
OP9-B100-DX	B	10	010 0	100	clockwise	154,78 €
OP9-A10-SX	A	1	001 0	300	anticlockwise	154,78 €
OP9-A30-SX	A	3	003 0	300	anticlockwise	154,78 €
OP9-A40-SX	A	4	004 0	200	anticlockwise	154,78 €
OP9-A50-SX	A	5	005 0	200	anticlockwise	154,78 €
OP9-A100-SX	A	10	010 0	100	anticlockwise	154,78 €
OP9-B10-SX	B	1	001 0	300	anticlockwise	154,78 €
OP9-B30-SX	B	3	003 0	300	anticlockwise	154,78 €
OP9-B40-SX	B	4	004 0	200	anticlockwise	154,78 €
OP9-B50-SX	B	5	005 0	200	anticlockwise	154,78 €
OP9-B100-SX	B	10	010 0	100	anticlockwise	154,78 €