Bipod support base

Plastic

ESCB

- ***Combined bipod support part***
- *Component for conveyor structure*
- *For round tube*
- *Materials*
  Body: Reinforced polyamide
  Inserts: Nickel brass
  Screws: stainless steel




Accessories

- *Compatible* **PR** *Feet*

Typical application





DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	ØDF	Max. load resistance. FM (N)	Max. sliding force FD(N)	Max. working load FT (N)	Weight (kg)	Stock*	Price each 1 to 4
ESCB-42	42,4	13000	7500	7500	1,60	✔	42,45 €
ESCB-48	48,3	13000	7500	8000	1,60	✔	42,45 €
ESCB-50	50,9	13000	7500	8500	1,60	✔	43,58 €
ESCB-60	60,3	13000	7500	9000	1,60	✔	42,45 €

**Depending on availability - Dimensions in mm*

Altri prodotti...


UGH25

Unità di guida tipo H, Per martinetti Ø25


RAG

Guida di scorrimento a rullini,


H1

Ingranaggio elicoidale ad assi incrociati a 90°, Acciaio 20NCD2


BMF

Manopola, Zigrinata - Passante


GSI_A

Molla a gas regolabile inox, Inox


RPP


Piastra di giunzione per cinghia RPP, RPP14


SH2

Ingranaggio elicoidale ad assi paralleli, Acciaio 20NCD2


CDC

Molla di compressione conica, Conica


AWMP

Albero in alluminio per guida lineare, Alluminio


RTE

Rotex®, elastico, acciaio


BOX-TOR-DRING

Valigetta di guarnizioni toriche in nitrile, Flange seals


H0

Ingranaggio elicoidale ad assi incrociati a 90°, Acciaio 20NCD2

Prodotti correlati


PR40

Piede fissabile con snodo - poliammide, Ø 40


ESSB

Base di sostegno, Bipiede singolo