

Lifting sling with 2 eyelinks

New


SGL1

Purple range SWL 1000kg

- **Lifting element**
- High quality polyester lifting slings according to European Industry regulations UNI EN 1492-1
- Flat sling
- Wide 30mm
- SWL: safe working load



F Max
1000kg



0°



F

0°



F x 0,8

≤6°



F x 2

0° to 45°



F x 1,4

45° to 60°



F

0° to 45°



F x 1,4

0° to 45°



F x 1,12

45° to 60°



F

45° to 60°



F x 0,8


DISCOUNTS

Qty	1+	4+	10+	15+
Disc.	List	-5%	-10%	On request


Part number	Fmax (kg)	Length L	W	E	L1	W2	Price each 1 to 3
SGL1-1000	1000	1000	30	7	200	15	
SGL1-1500	1000	1500	30	7	200	15	
SGL1-2000	1000	2000	30	7	200	15	
SGL1-2500	1000	2500	30	7	200	15	
SGL1-3000	1000	3000	30	7	200	15	
SGL1-4000	1000	4000	30	7	200	15	

Dimensions in mm

- **Lifting element**
- High quality polyester lifting slings according to European Industry regulations UNI EN 1492-1
- Flat sling
- Wide 60mm
- SWL: safe working load



F Max
2000kg



0°



F

0°



F x 0,8

≤6°



F x 2

0° to 45°



F x 1,4

45° to 60°



F

0° to 45°



F x 1,4

0° to 45°



F x 1,12

45° to 60°



F

45° to 60°



F x 0,8

DISCOUNTS

Qty	1+	4+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	Fmax (kg)	Length L	W	E	L1	W2	Price each 1 to 3
SGL2-1000	2000	1000	60	7	300	30	
SGL2-1500	2000	1500	60	7	300	30	
SGL2-2000	2000	2000	60	7	300	30	
SGL2-2500	2000	2500	60	7	300	30	
SGL2-3000	2000	3000	60	7	300	30	
SGL2-4000	2000	4000	60	7	300	30	
SGL2-5000	2000	5000	60	7	300	30	
SGL2-6000	2000	6000	60	7	300	30	
SGL2-8000	2000	8000	60	7	300	30	
SGL2-10000	2000	10000	60	7	300	30	
SGL2-12000	2000	12000	60	7	300	30	

Dimensions in mm

Lifting sling with 2 eyelinks

New

SGL3

Yellow range SWL 3000kg


- Lifting element

- High quality polyester lifting slings according to European Industry regulations UNI EN 1492-1
- Flat sling
- Wide 90mm
- SWL: safe working load



F Max
3000kg

F



0°



F

0°



F x 0,8

≤6°



F x 2

0° to 45°



F x 1,4

45° to 60°



F

0° to 45°



F x 1,4

0° to 45°



F x 1,12

45° to 60°



F

45° to 60°



F x 0,8

DISCOUNTS

Qty	1+	4+	10+	15+
Disc.	List	-5%	-10%	On request


Part number	Fmax (kg)	Length L	W	E	L1	W2	Price each 1 to 3
SGL3-1000	3000	1000	90	7	350	30	
SGL3-2000	3000	2000	90	7	350	30	
SGL3-3000	3000	3000	90	7	350	30	
SGL3-4000	3000	4000	90	7	350	30	
SGL3-5000	3000	5000	90	7	350	30	
SGL3-6000	3000	6000	90	7	350	30	
SGL3-8000	3000	8000	90	7	350	30	
SGL3-10000	3000	10000	90	7	350	30	
SGL3-12000	3000	12000	90	7	350	30	

Dimensions in mm

- **Lifting element**
- High quality polyester lifting slings according to European Industry regulations UNI EN 1492-1
- Flat sling
- Wide 120mm
- SWL: safe working load



F Max
4000kg



0°



F

0°



F x 0,8

≤6°



F x 2

0° to 45°



F x 1,4

45° to 60°



F

0° to 45°



F x 1,4

0° to 45°



F x 1,12

45° to 60°



F

45° to 60°



F x 0,8

DISCOUNTS

Qty	1+	4+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	Fmax (kg)	Length L	W	E	L1	W2	Price each 1 to 3
SGL4-1000	4000	1000	120	7	425	40	
SGL4-1500	4000	1500	120	7	425	40	
SGL4-2000	4000	2000	120	7	425	40	
SGL4-2500	4000	2500	120	7	425	40	
SGL4-3000	4000	3000	120	7	425	40	
SGL4-4000	4000	4000	120	7	425	40	
SGL4-5000	4000	5000	120	7	425	40	
SGL4-6000	4000	6000	120	7	425	40	
SGL4-8000	4000	8000	120	7	425	40	
SGL4-10000	4000	10000	120	7	425	40	
SGL4-12000	4000	12000	120	7	425	40	

Dimensions in mm

Lifting sling with 2 eyelinks


New

SGL5

Red range SWL 5000kg



- Lifting element

- High quality polyester lifting slings according to European Industry regulations UNI EN 1492-1
- Flat sling
- Wide 150mm
- SWL: safe working load



F Max
5000kg

F



0°



F

0°



F x 0,8

≤6°



F x 2

0° to 45°



F x 1,4

45° to 60°



F

0° to 45°



F x 1,4

0° to 45°



F x 1,12

45° to 60°



F

45° to 60°



F x 0,8

DISCOUNTS

Qty	1+	4+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	Fmax (kg)	Length L	W	E	L1	W2	Price each 1 to 3
SGL5-1000	5000	1000	150	7	500	50	
SGL5-1500	5000	1500	150	7	500	50	
SGL5-2000	5000	2000	150	7	500	50	
SGL5-2500	5000	2500	150	7	500	50	
SGL5-3000	5000	3000	150	7	500	50	
SGL5-4000	5000	4000	150	7	500	50	

Dimensions in mm

Altri prodotti...



Ingranaggio dritto in plastica, Plastica lavorata (delrin)



Manicotto esagonale maschiato, Esagonale - inox



Piede snodato con base stampata Ø100, 15000N



Maniglia a ponte - Multi-settore, Foro liscio



Ingranaggio elicoidale ad assi paralleli, Acciaio 20NCD2



Supporto per sensore Ø12, Ø12



Riduttore a rinvio angolare a L o a T, fino a 87,3 Nm



Spazzola al metro, Polipropilene nero striato (PP)



Ruota fissa con piastra, Inox -



Ruota girevole a foro centrale, Acciaio -



Ingranaggio conico spiroidale, 1:1



Vite senza fine di precisione, Acciaio

Prodotti correlati