New Rectangular hinge, drilled or countersunk

For built-in doors

CHA

- ***Drilled or countersunk hinge***
- *Materials:*
  Stainless steel (304)
  Natural finish







DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	A	B	C	ØD	S	Type	Weight (g)	Price each 1 to 5
CHA60-35-F/SS	60	35	1	2	4	Countersunk	20	5,68 €
CHA60-35-P/SS	60	35	1	2	4	Drilled	20	5,68 €

Dimensions in mm

Altri prodotti...



Cerniera a molla, avvitabile



Riduttore inox a ruota e vite senza fine, fino a 152 Nm



Perno autobloccante inox 303, Inox 303



Cinghia di trasmissione RPP, RPP8



Anello di sollevamento, Inox



Piede snodato tutto inox Ø30, Ø 30



Pignone tendicatena, Per applicazioni correnti



Tenditore rigido, Fisso



Piastra di giunzione per cinghia RPP, RPP5



Ruota di precisione, Bronzo



Piede fissabile con snodo - poliammide, Ø



Ingranaggio interno, Acciaio 20NCD2

Prodotti correlati



Cerniera, Quadrata con rivetto e fori



Cerniera, Quadrata con rivetto senza fori