Ste Sta Square hinge with riveted pin, not drilled

For built in doors

CHAC-NP

- **Riveted pin**
- Material :
  CHAC-NP: Steel hinge
  CHAC-NP/SS: Stainless steel 304
- Brut finish







DISCOUNTS

Qty.	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	A	B	C	ØD	Weight (g)	Stock*	Price each 1 to 5
Steel							
CHAC4040-NP	40	40	2	4	34	✔	8,69 €
CHAC5050-NP	50	50	2	6	61	✔	10,68 €
CHAC6060-NP	60	60	2	6	82	✔	11,80 €
Stainless steel							
CHAC4040-NP/SS	40	40	2	4	34	✔	14,69 €
CHAC5050-NP/SS	50	50	2	6	61	✔	16,85 €
CHAC6060-NP/SS	60	60	2	6	82	✔	19,03 €

**Depending on avaibility - Dimensions in mm*

Altri prodotti...



TK

Manicotto a sfere autoallineante Topball, Autoallineante,



PTMR

Piede regolabile, threaded stud



PDM_PDV

Detectable plastic palm grip, by metal detectors



PSPE22

Conical flexible shaft handlee Ø22, Black PVC



SBF

Sealed flange bearing unit for Food Industry, cover



M0

Ruota per vite senza fine , Plastica lavorata (delrin)



CCL

Capocorda ad occhiello, Acciaio



PP50

Riduttore a ruota e vite senza fine, da 6.50 a 12.80 Nm



ECF

Rivetto rivestito in gomma di fissaggio, Elastomero in



WTM

Rondella per serraggio - DIN6340, Acciaio



PTA100

Piede snodato con base stampata Ø100, 15000N



BOX-CS

Fascette di serraggio, Valigetta di fascette acciaio

Prodotti correlati



CHAC4040NP

Cerniera, Quadrata con rivetto senza fori



CHAC4040SS

Cerniera, Quadrata con rivetto e fori