Idler sprocket for plate chain

For chain range 881 TAB — PR881

- ***For use with CAP881T/SS plate chains***
- *Materials:*
  Reinforced polyamide
  Stainless steel screws
- *Operating temp.: -10°C to +120°C*
- *For dimensions and bore tolerances, please refer to technical pages*

Advantage

- *Two part design facilitates easy assembly*

Easy assembly





Two part design



DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	No. of teeth	ØDE	ØDP	Bore ØA	Weight (kg)	Price each 1 to 4
PR881-21-25	21	129	129,26	25	0,37	27,79 €
PR881-21-30	21	129	129,26	30	0,37	27,79 €
PR881-21-35	21	129	129,26	35	0,37	27,79 €
PR881-21-40	21	129	129,26	40	0,37	27,79 €
PR881-21-45	21	129	129,26	45	0,37	27,79 €
PR881-23-25	23	141	141,22	25	0,44	28,85 €
PR881-23-30	23	141	141,22	30	0,44	28,85 €
PR881-23-35	23	141	141,22	35	0,44	28,85 €
PR881-23-40	23	141	141,22	40	0,44	28,85 €
PR881-23-45	23	141	141,22	45	0,44	28,85 €
PR881-25-25	25	153	153,20	25	0,49	30,30 €
PR881-25-30	25	153	153,20	30	0,49	30,30 €
PR881-25-35	25	153	153,20	35	0,49	30,30 €
PR881-25-40	25	153	153,20	40	0,49	30,30 €
PR881-25-45	25	153	153,20	45	0,49	30,30 €

Dimensions in mm

Altri prodotti...


DOMI50

Kit di raccordo, Kit di raccordo XY


BWU

Guida lineare di precisione, da 1510 N a 10500 N


MEB

Ingranaggio conico in plastica stampata, 1:1


SUA4_L

Giunzione per catena al metro, Falsa maglia - acciaio


TBEBASE

Base plate for economic mini-table, Allows X-Y cross tables


BH02

Cuscinetto radiale flangiato, Montaggio con circlips


ASL

Anello di sollevamento, a 45° a saldare


VELM6

Supporto avvitabile per rotolo a strappo fermacavi, Poliammide


H1

Ingranaggio elicoidale ad assi incrociati a 90°, Plastica lavorata ...


BS2

Panamech, Multi-Beam, Alluminio - con vite a pressione


KB_OP

Manicotto a sfere di precisione, Di precisione - acciaio


H02SS

Giunto cardanico semplice ad aghi - inox, Sollecitazioni importante ...

Prodotti correlati


CAP881

Catena a tapparella, Stretta serie 881


PT881

Pignone di trazione, Serie 881