# Fastener for aluminium profile

## PRF MiniTec — Universal fastener

## FIXUNI

### Uses

- Low cost fastening requiring little preparation
- Used for different assembly types

### Central hole

- Directly accepts M8 screws

**Quick-fixing**












### Assembly

1. Tap the central hole of the first profile (1) using a fluteless M8 tap.
   Lightly attach the fastener to the end of the profile using the M8 screw (do not screw in completely)
2. Attach the second profile (2) in the required position.
3. Tighten the M8 grubscrew with an SW4 hexagonal key or the PRF-TOOL-H4 tool.
   Max. Suggested torque 12Nm

### Advantages

- Ends of profiles remain available
- Fastener is not visible
- Profiles can be repositioned/adjusted at any time
- Assembly will not twist
- Maximum load allowed: 6000N
- Cross joints in 3 dimensions can be created
- Joint can conduct electricity for bonding purposes.

# Fastener for aluminium profile

## Universal fastener

**MiniTec PRF**

**FIXUNI**

### Profile assembly

- Can be used to join all profile types
- Use multiple fasteners for longer lengths
- Materials:
- Fastener: electroplated chromed steel or stainless steel
- Round headed M8 screw, 25mm long.



### Assembly

- Lightly attach the fastener into the slot on the profile (do not tighten )
- Slide the fastener in the slot to the required position
- Tighten the M8 grubscrew with an SW4 hexagonal key or the **PRF-TOOL-H4** tool







**DISCOUNTS**

| Qty. | 1+ | 50+ | 100+ |
|---|---|---|---|
| Disc. | List | -5% | On request |

| Part number | For profile | Tightening torque (Nm) | Weight (kg) | Stock* | Price each 1 to 49 |
|---|---|---|---|---|---|
| PRF-FIX-UNI | All type of PRF profile | 10,0 | 0,029 | ✔ | 5,18 € |
| PRF-FIX-UNI/SS | Stainless PRF/SS profile | 01,2 | - | ✔ | 11,40 € |

**Depending on availability - Dimensions in mm*

# Altri prodotti...



EP7

Indicatore di posizione elettronico, 5 cifre



BH02

Cuscinetto radiale flangiato, Montaggo con circlips



SRG

Chiusura a leva regolabile, Corsa da 77,3mm a 83mm



PX

Riduttore a ruota e vite senza fine, Albero doppio in uscita per rid...



GTCSS

Rullo tendicinghia, Per ambienti aggressivi



RHT

Ruota alte temperature, fino a 200kg



PM4

Vite senza fine, Acciaio non temprato



CLSCLP_SS

Perno serie corta inox, Inox - serie corta



KH

Manicotto a sfere, Leggera



SVR15

Martinetto a vite - Vite rotante, Con



BPFL

Supporto a flangia ovale con cuscinetto,



PSPD18

Manopola a pressione, PVC nero

## Prodotti correlati



PRF1932

Profilato alluminio standard, 19 x 32 mm



PRF4545

Profilato inox standard, 45 x 45 mm



PRF_FIX_STD

Fissaggio, Fissaggio standard



PRF_FIX_ANG

Fissaggio, Fissaggio angolare