
Shaft support for aluminium profile

Stock*

PRFPSA MiniTec Z12

For attaching a guidance shaft to a profile

- ***Support profile for linear guide shafts***
- *Materials:*
  Profile: anodised aluminium E6/V1
  Steel shaft: Cf53 hardened (62 +/-2 HRC) Stainless steel shaft: hardened stainless steel X90CrMoV18 (57 +/-2 HRC)
  Shaft end stop: grey power coated aluminium
  (Fixing kit supplied)




Assembly

- *Insert the shaft support profile into the profile slot*
- *Secure with M5x10 grubscrews*
- *Insert the shaft into the support profile with the aid of a plastic mallet if necessary*


Accessories

- *Roller* **PRF-GAL-12**
- *Shaft end stop* **PRF-12-AA**





PRF-12-PSA



PRF-12-AA

DISCOUNTS

Qty.	1+	50+	100+
Disc.	List	-5%	On request

DISCOUNTS SHAFTS Z

Qty.	1+	6+	20+	40+	60+	100+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	For profile	Material	Length	Weight (kg/m)	Stock*	Price each
Shaft support profile						
PRF-12-PSA	all types	-	3000	0,36	✔	22,85 €
Linear guidance shaft						
Z-12-3000A		steel	3000	0,89	-	46,08 €
Z-12-3000B		stainless steel	3000	0,89	-	148,34 €
Shaft end stop						
PRF-12-AA		-	-	0,03	-	6,20 €

**Depending on availability - Dimensions in mm*

Altri prodotti...



Vite trapezoidale acciaio, Acciaio semiduro - 1 filetto



Cerniera a testa piatta a saldare, Acciaio



Tavola lineare Drylin®, Economica



Rulliera, Senza guida laterale



Rinvio angolare ad albero cavo, fino a 1.77 Nm



Puleggia dentata di posizionamento tipo T, Serie economica - T5 allu...




Vite senza fine, Acciaio non temprato



Cinghia di trasmissione RPP, RPP14



Albero per riduttore a ruota e vite senza fine CHMR e CHM, Albero se...



Ingranaggio conico - Acciaio 60C40, 1:1



Boccola di posizionamento, Acciaio



Ingranaggio elicoidale ad assi paralleli, Plastica lavorata (delrin)

Prodotti correlati



Rotella per profilo alluminio, Rotella cava ø12



Rotella per profilo alluminio, per bloccaggio albero