
Cylindrical brush track

For gentle conveying and handling

RAG B

- ***Mini roller conveyor prevents damage to parts***
- *Surface-friendly fibre arrangement*
- *Dirt adhesion is prevented*
- *Reduced manual effort*
- *Easy handling in all direction*





Materials

- *Plastic roller, polyamide fibres*
- *Steel rail*

Advantages

- *Ideal for sensitive products*
- *Quiet conveying*





Typical application

DISCOUNTS

Qty	1+	2+	5+	10+	20+
Disc.	List	-5%	-11%	-14%	On request

Part number	Length L (mm)	Space between rollers (mm)	Nb of rollers	Load-bearing capacity per 1 m track (kg)	Price each.
Low density					
RAG-B30-2000	2000	66	30	25	
High density					
RAG-B60-2000	2000	33	60	50	

Dimension in mm

Altri prodotti...



DIV

Pistoncino a molla, Bloccabile - Acciaio



ERC

Terminale rapido per cavi, A forcella



ETQ

Porta etichette per profili alluminio, Porta etichette



ALIDR30

Alimentazione, 1,5 A and 2 A



SA_SAKH

Supporto per manicotto, Chiuso - carico leggero



PTAF100-PAMF100

Piede fissabile con base lamiera Ø100, Ø 100



G4-ECO

Ingranaggio dritto acciaio - serie ECO, Acciaio C45



OP7

Indicatore di posizione digitale (N. di giri), 5 cifre



BPTR

Tappo per tubo tondo, Standard



DZY

Piedino antivibrante cilindrico, Acciaio



RAG

Guida di scorrimento a rullini,



RBNtc

Ruota girevole a foro centrale, Acciaio - caucciù - a doppio blocca...

Prodotti correlati



RAGFLOW

Rotaia a rulli Floway2®, Rotaia a rulli



RAGFLOWsupport

Accessori per rotaia a rulli Floway2®, Roller track support



RAG

Guida di scorrimento a rullini,