
Connecting plate

PITCH
RPP5
RPP8
RPP14

For open belts RPP5M, RPP8M and RPP14M

- 5mm,8mm and 14mm pitches
- ***For linear movements***
- Rigid connecting plates
- Material : aluminium





Applications

- For closing an open belt
- To attach an open belt to a structure

Accessories

- **RPP../P** belts
- **HTD** pulleys





Typical application

DISCOUNTS

Qty.	1+	6+	20+
Disc.	List	-10%	On request

Part number	Pitch	F	d	B	A	S	C	Belt width	Price each 1 to 5
RPP5/15P	RPP5	6	5,5	3,25	41,5	8	34	15	10,82 €
RPP5/25P	RPP5	6	5,5	3,25	41,5	8	44	25	13,21 €
RPP8/20P	RPP8	8	9,0	5,00	66,0	15	45	20	36,26 €
RPP8/30P	RPP8	8	9,0	5,00	66,0	15	55	30	41,68 €
RPP8/50P	RPP8	8	9,0	5,00	66,0	15	75	50	55,34 €
RPP14/55P	RPP14	10	11,0	9,00	116,0	22	86	55	141,06 €
RPP14/85P	RPP14	10	11,0	9,00	116,0	22	116	85	185,51 €

Dimensions in mm

Altri prodotti...



Pignone a catena - acciaio, 8mm (DIN 05B-1)



Cerniera, Quadrata con rivetto senza fori



Perno folle inox, Standard - inox



Unità di guida per cilindrico, Colonna di guida



Mini martinetto motorizzato 4A, 4 ampere



Piastrina di riscontro, 12,13,18 e 20mm



Economic mini-table with trapezoidal leadscrew, 2kg



Cuscinetto a doppia corona di sfere, Radiale - Acciaio



Piedino antivibrante cilindrico, Inox



Maniglia a ripresa Hygienic Usit®, Inox




Puleggia dentata di posizionamento tipo



Cerniere e giunti, Con maniglia di serraggio

Prodotti correlati



Cinghia aperta al metro tipo RPP, RPP8 Poliuretano armatura in acciaio