Spherical ended stop for aluminium profiles New

ACL BTS — Clip-in mounting


- ***Rapid closing mechanism for doors***
- *Material*
  Black glass fibre reinforced nylon

Advantages


- *Suitable for PRF aluminium profiles*
- *Mounts in any position*


Info

- *No mounting screws supplied (see PRF-ECL-M6 and BHC6)*









DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Locknut	Retaining force (N)	Weight (g)	Price each 1 to 49
ACL-BTS-40/ZN	Chromed	40	45	4,45 €
ACL-BTS-40/SS	Stainless steel 304	40	45	6,68 €
ACL-BTS-50/ZN	Chromed	50	45	4,45 €
ACL-BTS-50/SS	Stainless steel 304	50	45	6,68 €

Dimensions in mm

New Closing system for use with aluminium profiles

Accessories for spherical end stop ACL BTS

- **Right angled bracket and spacer for fast closing mechanism**

Advantages


- Suitable for PRF aluminium profiles
- Mounts in any position

Info

- No mounting screws supplied (see PRF-ECL-M6 and BHC6)
- Not sold individually, contact us for details





ACL-BTS-ET




ACL-BTS-EQ


NEW !





ACL-BTS-ET





ACL-BTS-EQ

DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Version	Material	Weight (g)	Price each 1 to 49
ACL-BTS-ET	Spacer	Nylon	5	0,42 €
ACL-BTS-EQ	90° bracket	Chromed steel	72,4	2,49 €

Dimensions in mm

Altri prodotti...



VELprf

Supporto clip per rotolo a strappo fermacavi, Poliammide



BLH40

Rinvio angolare a L, da 3 a 10.30 Nm



CDGamme

Molla di compressione DIN2095, DIN 2095



PTRSS

Pignone tendicatena, Per ambienti aggressivi



SFE

Testa a snodo femmina, Inox / PTFE



TCL-ECL

Piede massiccio per carichi pesanti, Vite a registro




MRA_SS

Maglia rapida, Inox



DPAR_DKON

Piedino antivibrante parabolico, Acciaio



AC

Piastrina di riscontro, 15mm




PLA

Magnete piatto, Magnete piatto



PDM_PDV

Detectable plastic palm grip, blue thermoplastic



T5M_T10M

Cinghia aperta al metro tipo T, T5 Poliuretano armatura in acciaio

Prodotti correlati



PRF4545

Profilato alluminio standard, 45 x 45 mm



PRF_ECL

Fissaggio, Dado quadrato con linguetta - Acciaio



PRF-SMA

Sistema di chiusura per profili alluminio, Easily adjustable lock