

Spherical ended stop for aluminium profiles New

ACLBS

Clip-in mounting

- Rapid closing mechanism for doors
- Material
Black glass fibre reinforced nylon



NEW!

Advantages

- Suitable for PRF aluminium profiles
- Mounts in any position

Info

- No mounting screws supplied (see PRF-ECL-M6 and BHC6)



DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Locknut	Retaining force (N)	Weight (g)	Price each 1 to 49
ACL-BTS-40/ZN	Chromed	40	45	4,45 €
ACL-BTS-40/SS	Stainless steel 304	40	45	6,68 €
ACL-BTS-50/ZN	Chromed	50	45	4,45 €
ACL-BTS-50/SS	Stainless steel 304	50	45	6,68 €

Dimensions in mm



Closing system for use with aluminium profiles

Accessories for spherical end stop **ACLBS**

- Right angled bracket and spacer for fast closing mechanism

Advantages

- Suitable for PRF aluminium profiles
- Mounts in any position

Info

- No mounting screws supplied (see PRF-ECL-M6 and BHC6)
- Not sold individually, contact us for details





ACL-BTS-ET





ACL-BTS-EQ

NEW!



ACL-BTS-ET



ACL-BTS-EQ

DISCOUNTS

Qty	1+	50+	100+
Disc.	List -5%	On request	

Part number	Version	Material	Weight (g)	Price each 1 to 49
ACL-BTS-ET	Spacer	Nylon	5	0,42 €
ACL-BTS-EQ	90° bracket	Chromed steel	72,4	2,49 €

Dimensions in mm

Altri prodotti...



G0

Ingranaggio dritto
acciaio, Acciaio
20NCD2



PSG125

Ingranaggio dritto di
precisione, Acciaio
20NCD2 cementato
temprato



PMC150_M16

Supporto antivibrante
a campana, Piastra a
base quadrata



AC

Piastrina di riscontro,
12mm



R206

Molla per stampi
ISO10243, Extra-forte



HG6-ECO

Ingranaggio dritto
acciaio - serie ECO,
Acciaio C45



PSG2

Ingranaggio dritto di
precisione, Acciaio
20NCD2 cementato
temprato



CHTRP

Riduttore a rinvio
angolare a L o a T,
fino a 9,1 Nm



BLHM60

Rinvio angolare, fino a
70 Nm



KBS_UU

Manicotto chiuso a
sfere inox di
precisione, Di



AC156-157

Riscontro per chiusura
a leva rigida ad
anello, 25.5mm



RPCpl

Ruota girevole a
doppio bloccaggio,
Acciaio - poliammide

Prodotti correlati



PRF4545

Profilato alluminio
standard, 45 x 45 mm



ACLBTS

Sistema di chiusura,
Blocca porta a sfera