

# Angular clamp




## BAN

## For profile systems

- Easy to add to most profiles
- Material :  
Aluminium
- Fixing kit not supplied

**NEW!**




### Advantages


- Wide range of assembly possibilities
- **Angular clamp** : space saving when assembling compact
- **Universal angular clamp** : Compatible with 20mm and 300 mm profile systems with oblong holes
- **Adjustable angular clamp** : Flexible positioning of gripping elements due to use of rectangular holes

### Accessories


- PRF-ECLM8 nut
- M8 screw, length 20-22mm



Angular clamp



Universal angular clamp



Adjustable angular clamp

### DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	Type	ØA	B	C	D	L	H	F	N	Weight (g)	Price each 1 to 9
BAN-20	-	20	45	24,5	12	-	20	-	-	103	26,21 €
BAN-30	-	30	68	34	17	-	20	-	-	172	30,89 €
BAN-20/U	universal	20	30	32-42	-	-	20	10	33	114	26,20 €
BAN-30/U	universal	30	35	37-47	-	-	20	10	42	122	32,10 €
BAN-20/A	adjustable	20	30	21	100	130	12,5	-	-	140	32,29 €
BAN-30/A	adjustable	30	35	25,5	100	159	20	10	42	213	37,57 €

Dimensions in mm

## Altri prodotti...



SLBS  
Pistoncino a molla,  
Tutto inox



CHM30  
Riduttore a ruota e  
vite senza fine, fino a  
28 Nm




AT10courroie  
Cinghia di  
posizionamento AT,  
AT10 Poliuretano  
armatura in acciaio



VPR  
Vite ad alette  
Hygienic Usit®, Inox




ACM\_AZ  
Aggancio per tirante  
chiusura in gomma,  
Aggancio



PF20NM  
Riduttore a ruota e  
vite senza fine, fino a  
5 Nm



MSP38  
Inserto con piastrina a  
incollare  
Masterplate®,  
Cilindrico Ø38 con...



CRM  
Cremagliera in nylon  
stampato, Nylon



TCXR  
Tenditore per catena  
automatico, Con  
pignone acciaio



PTA50  
Piede snodato con  
base stampata Ø50, Ø  
50



P40  
Riduttore a ruota e  
vite senza fine, fino a  
118 Nm



BTESS  
Tenditore automatico  
universale per  
tenditore, Per  
ambienti aggressivi

## Prodotti correlati



BAN  
Connettore / supporto  
per profili alluminio,  
Regolabile



PRF\_ECL  
Fissaggio, Dado  
quadrato con  
linguetta - Acciaio