

# Mushroom knob with male thread and high head

## BCFHUSS

## Hygienic Usit®


- **Mushroom knob with a male thread and high head for use with Hygienic Usit® sealing washers®**
- The high head makes this mushroom knob ideal for manual lateral movements.
- Fully polished surface with a roughness much lower than Ra0.8µm.
- Material:  
Stainless steel 1.4404 (316L)  
Mirror polished finish

### Advantages

- Regardless of the mounting position of the mushroom knob, dirt and residue from product or cleaning material will not adhere. This guarantees easy cleaning.
- USIT® Hygienic sealing washers are used to seal the screwed connection.
- The stem of the mushroom knob is specially designed to ensure an almost cavity free seal thus meeting hygiene requirements.

### Accessory

- RDE sealing washers (see pages 37 à 39)



### DISCOUNTS

Qty	1+	6+	10+	25+
Disc.	Prix	-5%	-10%	On request

Part N°	ØD	ØD1	ØD2	H	H1	L	T	R	R1	Price each
										1 to 4
BCFH-4/HUSS	M4	20	10,8	19	8	8	7	3	0,45	13,02 €
BCFH-5/HUSS	M5	21	11,8	21	10	10	9	3	0,50	14,10 €
BCFH-6/HUSS	M6	25	14,2	25	12	12	11	3	0,55	15,68 €
BCFH-8/HUSS	M8	33	18,0	33	15	16	15	4	0,60	26,40 €
BCFH-10/HUSS	M10	40	22,3	40	19	20	19	4	0,75	28,18 €

All dimensions in mm

## Altri prodotti...



SSB

Ingranaggio conico  
inox, 1:1




NPTR10

Connettore rinvio  
d'angolo, Regolabile



CLM

Attacco per forcella,  
Corta inox



QNUP

Cuscinetto a singola  
corona di rulli  
cilindrici, Anello  
interno con ...



EHD06

Riduttore coassiale,  
da 8 a 19 Nm



S4

Pignone a catena -  
Inox, 4mm



SERB

Serratura a camme,  
Serratura a camme




AC

Piastrina di riscontro,  
15mm



MDB\_MTB

Ingranaggio conico in  
plastica stampata, 2:1



RPP14

Cinghia di  
trasmissione RPP,  
RPP14



CCL


Capocorda ad  
occhiello, Acciaio



CLG1

Ingranaggio dritto in  
plastica stampata ,  
Nylon stampato

## Prodotti correlati



RDE-W

Rondella di tenuta  
Hygienic Usit®, Inox -  
EPDM bianco



RDE-B

Rondella di tenuta  
Hygienic Usit®,  
Stainless steel - EPDM  
blu



BCTH

Pomello a fungo  
Hygienic Usit®, Con  
foro filettato e collare  
alto