

# Knurled knob, male

## BMM Technopolymer, steel or stainless steel stud


### - Small fixing knob

#### - Materials:

Black polyamide, matt surface finish  
Threaded stud: chromed steel  
or stainless steel

### Info

- Can be used with **BMF** female knurled knobs to make a manual bolted assembly



### DISCOUNTS

Qty	1+	10+	20+	50+	100+	200+
Disc.	Net	-5%	-10%	-15%	-20%	On request

Part N°		Weight							Price each 1 to 9	
Steel	Stainless steel	ØA	ØB	C	ØD	L	F	(g)	Acier	Inox
BMM15-M4-10		15	11	14	M4	10	7	4	1,18 €	
BMM15-M4-15		15	11	14	M4	15	7	4	1,26 €	
BMM15-M5-10		15	11	14	M5	10	7	4	1,22 €	
BMM22-M4-10		22	15	14	M4	10	6	6	1,26 €	
BMM22-M4-25		22	15	14	M4	25	6	6	1,34 €	
BMM22-M5-10	BMM22-M5-10/SS	22	15	14	M5	10	6	7	1,26 €	3,31 €
BMM22-M5-15		22	15	14	M5	15	6	7	1,26 €	
BMM22-M6-10		22	15	14	M6	10	6	8	1,34 €	
BMM22-M6-20		22	15	14	M6	20	6	9	1,34 €	
BMM22-M6-30		22	15	14	M6	30	6	11	1,43 €	
BMM22-M6-40		22	15	14	M6	40	6	13	1,47 €	
BMM26-M5-10		26	16	15	M5	10	6	9	1,47 €	
BMM26-M5-25		26	16	15	M5	25	6	11	1,47 €	
BMM26-M6-10		26	16	15	M6	10	6	10	1,47 €	
BMM26-M6-20	BMM26-M6-20/SS	26	16	15	M6	20	6	12	1,47 €	3,43 €
BMM26-M6-40		26	16	15	M6	40	6	15	1,55 €	
BMM26-M8-25		26	16	15	M8	25	6	17	1,63 €	
BMM32-M6-20		32	19	18	M6	20	8	14	1,63 €	
BMM32-M6-40		32	19	18	M6	40	8	18	1,71 €	
BMM32-M8-15		32	19	18	M8	15	8	19	1,79 €	
BMM32-M8-40		32	19	18	M8	40	8	27	1,92 €	

All dimensions in mm

## Altri prodotti...



G-ECO15

Ingranaggio dritto  
acciaio - serie ECO,  
Acciaio C45



NCT

Giunto di  
collegamento, Ad  
angolo fisso



T10\_21\_AL

Puleggia dentata di  
posizionamento tipo  
T, Serie economica -  
T10 all...



GCL

Guida lineare a sfere  
Eco, economica



GMK17\_RG

Morsetto di giunzione,  
Per guida prodotto  
laterale



MHSC

Giunto flessibile a  
disco semplice, Disco  
semplice



COA-COG

Staffa di montaggio  
per molla a gas,  
Staffa di montaggio  
piana per s...



M2

Ruota per vite senza  
fine, Bronzo




DEP

Attrezzi Hygienic  
Usit® and Hygienic



CHAEpac

Square decorative  
screwed hinges,



RPP5

Cinghia di  
trasmissione RPP,



CLLCLLP

Perno serie lunga,  
Acciaio - serie lunga

## Prodotti correlati



BMF

Manopola, Zigrinata -  
Cieco



BMF

Manopola, Zigrinata -  
Passante