

Right angled bracket for aluminium profiles

ACLEPP Connecting bracket for connecting 2 profiles

- To join 2 profiles at 90°
- Material
Anodised aluminium
For use with single slot profiles

Advantages

- Suitable for use with PRF aluminium profiles

Info

- No mounting screws supplied




ACL-EPP2-4545




ACL-EPP4-4590

NEW!



ACL-EPP2- 4545



ACL-EPP4-4590

DISCOUNTS

Qty	1+	50+	100+
Disc.	List -5%	On request	

Part number	Version	L	B	H	A	C	ØD	Weight (g)	Price each 1 to 49
ACL-EPP2-4545	2 holes	45	41	6	-	22,5	9	55	2,65 €
ACL-EPP4-4590	4 holes	90	41	6	45	22,5	9	112	5,27 €

Dimensions in mm

Right angled bracket for aluminium profiles

Connecting bracket for connecting 2 profiles **ACLEPP**

- To join 2 profiles at 90°
- Material
Anodised aluminium
For use with dual slot profilest

Advantages

- Suitable for use with PRF4590 aluminium profiles

Info

- No mounting screws supplied





ACL-EPP4-9045




ACL-EPP8-9090

NEW!



ACL-EPP4-9045



ACL-EPP8-9090


DISCOUNTS

Qty	1+	50+	100+
Disc. List	-5%		On request

Part number	Version	L	B	H	A	C	ØD	Weight (g)	Price each 1 to 49
ACL-EPP4-9045	4 holes	45	86	6	45	22,5	9	112	5,45 €
ACL-EPP8-9090	8 holes	90	86	6	45	22,5	9	235	9,76 €

Dimensions in mm

Altri prodotti...



INO
Ingranaggio interno,
Plastica lavorata
(delrin)



UGPC
Unità di guida per
cilindrico, Cuscinetto
corto



ACL-PR
Elementi di giunzione,
Collegamento a 90°



SDG_SS
Supporto con tirante
ad occhio, Inox



LVT
Mini martinetto
motorizzato 4A, 4
ampere



PDM_PDV
Detectable plastic
palm grip, blue
thermoplastic



GE32
Chiusura a leva rigida
ad anello, Standard



SH1
Ingranaggio elicoidale
ad assi paralleli,
Plastica lavorata
(delrin)



SLH-M
Dado per bloccaggio a
leva, Dado con
estremità sferica



SNG
Cuscinetto ritto
polimero inox, Ghisa -
In 2 metà



MHMEP
Manovella ad
impugnatura girevole,
Preasata



PRF_GAL
Rotella per profilo
alluminio, Kit di
fissaggio per rotella
concentr...

Prodotti correlati



PRF4545
Profilato alluminio
standard, 45 x 45 mm