

Right angled bracket for aluminium profiles

ACLEPP Connecting bracket for connecting 2 profiles

- To join 2 profiles at 90°
- Material
Anodised aluminium
For use with single slot profiles

Advantages

- Suitable for use with PRF aluminium profiles

Info

- No mounting screws supplied




ACL-EPP2-4545





ACL-EPP4-4590


NEW!



ACL-EPP2- 4545



ACL-EPP4-4590



DISCOUNTS

Qty	1+	50+	100+
Disc.	List -5%	On request	

Part number	Version	L	B	H	A	C	ØD	Weight (g)	Price each 1 to 49
ACL-EPP2-4545	2 holes	45	41	6	-	22,5	9	55	2,65 €
ACL-EPP4-4590	4 holes	90	41	6	45	22,5	9	112	5,27 €

Dimensions in mm

Right angled bracket for aluminium profiles

Connecting bracket for connecting 2 profiles **ACLEPP**

- To join 2 profiles at 90°
- Material
Anodised aluminium
For use with dual slot profilest

Advantages

- Suitable for use with PRF4590 aluminium profiles

Info

- No mounting screws supplied





ACL-EPP4-9045




ACL-EPP8-9090

NEW!



ACL-EPP4-9045



ACL-EPP8-9090

DISCOUNTS

Qty	1+	50+	100+
Disc. List	-5%	-5%	On request

Part number	Version	L	B	H	A	C	ØD	Weight (g)	Price each 1 to 49
ACL-EPP4-9045	4 holes	45	86	6	45	22,5	9	112	5,45 €
ACL-EPP8-9090	8 holes	90	86	6	45	22,5	9	235	9,76 €

Dimensions in mm

Altri prodotti...



BPM-Z

Pressore a molla con intaglio e puntale a sfera, Corpo plastica + sf...



ZG4

Ingranaggio dritto in plastica, Plastica lavorata (delrin)



DOG316

Motoriduttore DC 12V e 24V DC, da 1.5 a 2 Nm




BAB

Perno autobloccante a sfere, Inox temprato



TUBE25_25


Tubo quadrato, Alluminio



H2

Ingranaggio elicoidale ad assi incrociati a 90°, Plastica lavorata

...




LAT2

Attuatore lineare a motore 2A, 2 ampere



BABTBSS

Perno autobloccante per foro cieco, Inox 303



M1

Vite senza fine , Plastica lavorata (delrin)



J65

Riduttore coassiale a treni paralleli, da 0.80 a 2.95 - a treni para...



VCMB

Vite di giunzione metallo/legno, Inox



LRRss

Interblocco di sicurezza, Chiusura a molla - inox

Prodotti correlati



PRF4545

Profilato alluminio standard, 45 x 45 mm