

Right angled bracket for aluminium profiles

ACLEPP Connecting bracket for connecting 2 profiles

- To join 2 profiles at 90°
- Material
Anodised aluminium
For use with single slot profiles

Advantages

- Suitable for use with PRF aluminium profiles

Info

- No mounting screws supplied




ACL-EPP2-4545





ACL-EPP4-4590


NEW!



ACL-EPP2- 4545



ACL-EPP4-4590



DISCOUNTS

Qty	1+	50+	100+
Disc.	List -5%	On request	

Part number	Version	L	B	H	A	C	ØD	Weight (g)	Price each 1 to 49
ACL-EPP2-4545	2 holes	45	41	6	-	22,5	9	55	2,65 €
ACL-EPP4-4590	4 holes	90	41	6	45	22,5	9	112	5,27 €

Dimensions in mm

Right angled bracket for aluminium profiles

Connecting bracket for connecting 2 profiles **ACLEPP**

- To join 2 profiles at 90°
- Material
Anodised aluminium
For use with dual slot profilest

Advantages

- Suitable for use with PRF4590 aluminium profiles

Info

- No mounting screws supplied





ACL-EPP4-9045




ACL-EPP8-9090

NEW!



ACL-EPP4-9045



ACL-EPP8-9090

DISCOUNTS

Qty	1+	50+	100+
Disc. List	-5%	-5%	On request

Part number	Version	L	B	H	A	C	ØD	Weight (g)	Price each 1 to 49
ACL-EPP4-9045	4 holes	45	86	6	45	22,5	9	112	5,45 €
ACL-EPP8-9090	8 holes	90	86	6	45	22,5	9	235	9,76 €

Dimensions in mm

Altri prodotti...



NPTR10

Connettore rinvio d'angolo, Regolabile



BPPE

Sfera portante, Leggero



AT5M AT10M

Cinghia aperta al metro tipo AT, AT10 Poliuretano armatura in acciaio



P45

Riduttore a ruota e vite senza fine, fino a 40 Nm



BCM_CC

Spazzola cilindrica modulare, Filo di crine di cavallo



BH02

Cuscinetto radiale flangiato, Montaggio con circlips



BOX-TOR-INCH

Valigetta di guarnizioni toriche in nitrile, For fasteners and fitting



PGM52-M4

Maniglia a ponte, Ottone



SHS

Vite a spalla inox 303, Inox 303




PRF_SDD

Supporto per sensore Ø12, Ø12



G4

Ingranaggio dritto acciaio, Acciaio 20NCD2



PRT-TO

Corona girevole Iglidur®, Con dentatura esterna- Iglidur®, allumini...

Prodotti correlati



PRF4545

Profilato alluminio standard, 45 x 45 mm