

Split shaft collar with clamp lever

BAG-MI

Steel

- Ensures a uniform distribution of the clamping force
- Clamps securely to any type of shaft
- Material:

Burnished steel (S250Pb)

Repeated operations





Advantages

- Fits perfectly on to the shaft with a high clamping force but without risk of damage

Info.

- Recommended shaft tolerance: h11



DISCOUNTS

| Qty | 1+ | 6+ | 20+ | 40+ |
|-------|----|------|------|------------|
| Disc. | | -15% | -20% | On request |

| Part number | ØD1 | ØD2 | B | ØR | Stock* | Price each 1 to 5 |
|-------------|-----|-----|----|-------|--------|-------------------|
| BAG1-010-MI | 10 | 24 | 9 | 44,1 | - | 14,83 € |
| BAG1-012-MI | 12 | 28 | 11 | 90,4 | ✓ | 15,16 € |
| BAG1-015-MI | 15 | 34 | 13 | 105,0 | - | 16,38 € |
| BAG1-016-MI | 16 | 34 | 13 | 105,0 | ✓ | 16,73 € |
| BAG1-018-MI | 18 | 36 | 13 | 105,7 | - | 17,46 € |
| BAG1-020-MI | 20 | 40 | 15 | 103,8 | ✓ | 18,26 € |
| BAG1-022-MI | 22 | 42 | 15 | 104,2 | - | 18,26 € |
| BAG1-025-MI | 25 | 45 | 15 | 104,8 | ✓ | 19,34 € |
| BAG1-028-MI | 28 | 48 | 15 | 106,8 | - | 19,34 € |
| BAG1-030-MI | 30 | 54 | 15 | 112,6 | ✓ | 22,20 € |
| BAG1-040-MI | 40 | 60 | 15 | 113,2 | - | 25,18 € |
| BAG1-050-MI | 50 | 78 | 19 | 150,2 | - | 46,79 € |

Dimensions in mm

Altri prodotti...



ALIDRP240

Alimentazione, 10 A



PRF_PL_4590

Elementi di giunzione,
Piastra di giunzione -
45x90 mm




NPTF30

Morsetto di
collegamento,
Distanziale Ø14 a Ø20



M0

Vite senza fine ,
Acciaio temprato



LAT1

Attuatore lineare a
motore 1A, 1 ampere



D-PAR_SS

Piedino antivibrante
parabolico, inox



PTAF100-PAMF100

Piede fissabile con
base lamiera Ø100, Ø
100



PV1R

Braccio portaventosa
orientabile, Serraggio
standard



BPTR_M

Tappo per tubo, Con
inserto maschiato



PTKss

Piede speciale
agroalimentare, Inox -
3-A standard



S_2RS

Cuscinetto radiale a
sfere, Inox



PLM-20SC

Magnete cilindrico di
fermo filettato,
Magnete di fermo
maschiato

Prodotti correlati



BAG-MISS

Anello di serraggio
con intaglio e
maniglia a leva, Inox



BAG

Anello di bloccaggio in
acciaio, Acciaio