



Mushroom knob with female thread and high head

Hygienic Usit®

BCTH_{HUSS}

- **Mushroom knob with a female thread and high head for use with Hygienic Usit® sealing washers**
- The high head makes this mushroom knob ideal for manual lateral movements.
- Fully polished surface with a roughness much lower than Ra0.8µm.
- Material:
Stainless steel 1.4404 (316L)
Mirror polished finish




Advantages

- Regardless of the mounting position of the mushroom knob, dirt and residue from product or cleaning material will not adhere. This guarantees easy cleaning.
- USIT® Hygienic sealing washers are used to seal the screwed connection.
- The base of the mushroom knob is designed to ensure an almost cavity free seal thus meeting hygiene requirements.

Accessory

- RDE sealing washers (see pages 37-39)



DISCOUNTS

Qty	1+	6+	10+	25+
Disc.	Net	-5%	-10%	On request

Part N°	ØD	ØD1	ØD2	H	H1	T	R	R1	Price each
									1 to 4
BCTH-4/HUSS	M4	20	10,8	19	8	10	3	0,45	10,84 €
BCTH-5/HUSS	M5	21	11,8	21	10	12	3	0,50	11,74 €
BCTH-6/HUSS	M6	25	14,2	25	12	12	3	0,55	13,07 €
BCTH-8/HUSS	M8	33	18,0	33	15	16	4	0,60	22,01 €
BCTH-10/HUSS	M10	40	22,3	40	19	20	4	0,75	23,47 €

All dimensions in mm

0 825 88 6000

Service 0,15 €/min
+ prix appel

Fax

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

49

Altri prodotti...



M1

Vite senza fine ,
Acciaio non temprato




CHMR30

Riduttore a ruota e
vite senza fine, fino a
28 Nm



DB

Ingranaggio conico in
acciaio, 2:1



PRF JL5

Panel accessories,
Guarnizione - Ø 5mm



HRV

Sistema di guida su
binario a V Simple
Select®, Binario con
carrello



BAP

Anello di bloccaggio,
Ø10 - Ø20



DOG316

Motoriduttore DC 12V
e 24V DC, da 1.5 a 2
Nm



BABS303

Perno autobloccante
inox 303, Inox 303



HTD8M_20

Puleggia dentata di
trasmissione tipo
HTD, HTD8 Ghisa



BFDdII

Boccola di fermo per
perno ad innesto,
Acciaio nichelato



RCC_RCX


Rondella sferica -
DIN6319, concava



PSG125HC

Ingran. dritto di
precisione trattato
skiving, Acciaio
20NCD2 cement...

Prodotti correlati



RDE-W

Rondella di tenuta
Hygienic Usit®, Inox -
EPDM bianco



RDE-B

Rondella di tenuta
Hygienic Usit®,
Stainless steel - EPDM
blu



BCFH

Pomello a fungo
Hygienic Usit®, Con
perno filettato e
collare alto