



Mushroom knob with female thread and high head

Hygienic Usit®

BCTH_{HUSS}

- **Mushroom knob with a female thread and high head for use with Hygienic Usit® sealing washers**
- The high head makes this mushroom knob ideal for manual lateral movements.
- Fully polished surface with a roughness much lower than Ra0.8µm.
- Material:
Stainless steel 1.4404 (316L)
Mirror polished finish




Advantages

- Regardless of the mounting position of the mushroom knob, dirt and residue from product or cleaning material will not adhere. This guarantees easy cleaning.
- USIT® Hygienic sealing washers are used to seal the screwed connection.
- The base of the mushroom knob is designed to ensure an almost cavity free seal thus meeting hygiene requirements.

Accessory

- RDE sealing washers (see pages 37-39)



DISCOUNTS

Qty	1+	6+	10+	25+
Disc.	Net	-5%	-10%	On request

Part N°	ØD	ØD1	ØD2	H	H1	T	R	R1	Price each
									1 to 4
BCTH-4/HUSS	M4	20	10,8	19	8	10	3	0,45	10,84 €
BCTH-5/HUSS	M5	21	11,8	21	10	12	3	0,50	11,74 €
BCTH-6/HUSS	M6	25	14,2	25	12	12	3	0,55	13,07 €
BCTH-8/HUSS	M8	33	18,0	33	15	16	4	0,60	22,01 €
BCTH-10/HUSS	M10	40	22,3	40	19	20	4	0,75	23,47 €

All dimensions in mm

Fax 0 825 88 6000
Service 0,15 €/min
+ prix appel

cial2@hpceurope.com

HPC SUPPLEMENT 2019

Altri prodotti...



PRF-P
Supporto piede, Per piedi o ruote



TCSH
Tenditore per catena automatico, Con pattino



NT121
Riduttore coassiale a treni paralleli, da 20 a 68 Nm - a treni paral...



HCLBDB
Sistema di chiusura per profili alluminio, Fermo a 2 sfere



SLB
Pistoncino a molla, inox



ZBconique
Ingranaggio conico in plastica, 1:1




ETQ
Porta etichette per profili alluminio, Porta etichette



HLC24
Rinvio angolare a dentatura spiroidale, Fino a 78Nm



COA-COG
Staffa di montaggio per molla a gas, Staffa di montaggio



M0
Coppia ruota e vite senza fine, Plastica lavorata (delrin)




PP35
Riduttore a ruota e vite senza fine, da 2.20 a 4.10 Nm



RJA00_28
Guarnizione in gomma, Da agganciare

Prodotti correlati



RDE-W
Rondella di tenuta Hygienic Usit®, Inox - EPDM bianco



RDE-B
Rondella di tenuta Hygienic Usit®, Stainless steel - EPDM blu



BCFH
Pomello a fungo Hygienic Usit®, Con perno filettato e collare alto