

Combination spanner



CM_{HD} Hygienic Usit[®] and Hygienic Design[®]

- Combination spanner to be used with protective inserts for mounting Hygienic Usit[®] and Hygienic Design[®] products

- Materials:

Spanner: Tool steel


Inserts: AlSi1MgMn

Advantages

- The protective caps have been specifically designed for fastening and un-fastening screwed connections with delicate surfaces.
- The protective caps will safely avoid the risk of contact corrosion with stainless steel screwed connections.
- The protective cap is safely held in the spanner thanks to its special form and a sprung clip.

Accessories

- * Use the CM/HD/CF insert with the open-ended spanner and the CM/HD/CO insert with the ring spanner. (cf. page 62)



DISCOUNTS

| | | | |
|-------|-----|-----|------------|
| Qty | 1+ | 5+ | 10+ |
| Disc. | Net | -5% | On request |

| Part N° | SW | SW2* | A | B | L | Price each |
|----------|----|------|------|------|-------|------------|
| | | | | | | 1 to 4 |
| CM-10/HD | 10 | 7 | 5,0 | 8,0 | 154,5 | 23,10 € |
| CM-11/HD | 11 | 8 | 5,5 | 8,4 | 168,5 | 28,54 € |
| CM-13/HD | 13 | 10 | 6,3 | 10,0 | 193,0 | 28,45 € |
| CM-16/HD | 16 | 13 | 7,0 | 11,4 | 230,5 | 29,79 € |
| CM-19/HD | 19 | 16 | 8,0 | 13,5 | 268,5 | 30,74 € |
| CM-21/HD | 21 | 18 | 8,5 | 13,7 | 292,0 | 46,20 € |
| CM-27/HD | 27 | 24 | 10,5 | 16,0 | 380,0 | 54,20 € |

All dimensions in mm

Altri prodotti...



PRESSHR

Pressa manuale da banco, Pressione fino a 500kg



PRF_PL_4590

Elementi di giunzione, Piastra di giunzione - 45x90 mm



CHA135

Cerniera ad avvitare, 135 gradi



RGS

Giunto senza gioco Rotex® GS, da 0.5 a 190Nm



ACLEFS

Elementi di ancoraggio, Standard



CHMBR

Braccio di reazione, Braccio di reazione per riduttori CHM e CHMR



CHTRP

Riduttore a rinvio angolare a L o a T, fino a 75,7 Nm



E40

Riduttore a rinvio angolare, da 2.30 a 20 Nm



PTR

Pignone tendicatena, Per applicazioni correnti



VPPTss

Volantino pieno con impugnatura girevole, Inox 304



GPBSS

Impugnatura sferica femmina filettata, Inox 304



HTD8M_30


Puleggia dentata di trasmissione tipo HTD, HTD8 Acciaio

Prodotti correlati



VTSM

Ball head screws Hygienic Design®, Inox



CM_CO

Attrezzi Hygienic Usit® and Hygienic Design®, Protective inserts f...



CM_CO

Attrezzi Hygienic Usit® and Hygienic Design®, Protective inserts f...