

Knurled threaded torque Knob

BSC

Adjustable torque

- **Knurled knob with coloured insert**

- **Materials:**

Dark grey thermoplastic


Thread: steel blue chromed

Info.

- The required torque is adjusted by means of a screw.
- As soon as this torque is reached, the knurled knob will start to slip.

Options

- Versions with different coloured inserts are available, signal red, dark grey, yellow



DISCOUNTS

Qty	1+	6+	10+	25+
Disc.	List	-5%	-10%	On request

Part number	ØD	L	ØD1	ØD2	ØD3	ØD4	H	H1	T	Torque range (Nm)	Price each 1 to 5
Grey insert											
BSC26-M5-30	M5	30	26	18	23	16	27	10,5	5	0,1 - 0,3	45,16 €
BSC26-M5-50	M5	50	26	18	23	16	27	10,5	5	0,1 - 0,3	45,42 €
BSC26-M6-30	M6	30	26	18	23	16	27	10,5	6	0,1 - 0,3	45,16 €
BSC34-M6-40	M6	40	34	22	31	20	37,5	14,5	10	0,1 - 0,3	71,14 €
BSC34-M6-50	M6	50	34	22	31	20	37,5	14,5	10	0,1 - 0,3	45,42 €
BSC34-M6-60	M6	60	34	22	31	20	37,5	14,5	10	0,1 - 0,3	50,15 €
BSC34-M8-40	M8	40	34	22	31	20	37,5	14,5	14	0,1 - 0,3	49,78 €
BSC34-M8-60	M8	60	34	22	31	20	37,5	14,5	14	0,1 - 0,3	50,15 €

Dimensions in mm

Altri prodotti...




SHN

Dado esagonale -
DIN934, Acciaio (Class
6[8])



SH1

Ingranaggio elicoidale
ad assi paralleli,
Plastica lavorata
(delrin)



RIMtce

Ruota di livellamento,
Con foro centrale



CABtool

Attrezzi per cavi,
Attrezzi per
crimpatura



BFDdII

Boccola di fermo per
perno ad innesto,
Acciaio nichelato



RT70

Calettatore di
bloccaggio, Coppia
media/elevata



BEF

Vite a ricircolo di sfere
miniatura, Supporto
con cuscinetto



DOMI30

Kit di raccordo, Kit di
raccordo XZ



SSE

Snodo sferico inox,
Inox/PTFE



SER69K

Chiusura 1/4 di giro
per agroalimentare,



SSG2_304L

Ingranaggio dritto
Inox, Inox 304L



EBH

Dado cieco Hygienic
Design®, Con collare

Prodotti correlati



BSCf

Manopola, Con coppia
regolabile