Simple support base (bipod)

Stock Pla

ESSBNV


Plastic

- ***Bipod support base***
- *Component for conveyor structure*
- *For round tube*
- *Materials*
  Body: reinforced polyamide
  Screws: stainless steel 304

Accessories

- *Add compatible* **PR** *feet to order* ***(tome 5 p.169)***





DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	ØDF	Max. load resistance FM (N)	Max. working load FT (N)	Weight (kg)	Price each 1 to 4
ESSB-42/NV	42,4	15800	9600	0,612	43,57 €
ESSB-48/NV	48,3	15800	9600	0,612	43,57 €
ESSB-50/NV	50,8	15800	9600	0,612	43,57 €
ESSB-60/NV	60,3	15800	9600	0,752	43,57 €

Dimensions in mm

Bipod support base

Plastic

ESCBNV

- ***Combined bipod support part***
- *Component for conveyor structure*
- *For round tube*
- *Materials*
  Body: reinforced polyamide
  Screws: stainless steel 304

Accessories


- *Add compatible PR feet to order* ***(tome 5 p.169)***






Typical application

FM | FT





DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	ØDF	ØDH	Max load resistance.FM (N)	Max. working load FT (N)	Weight (kg)	Price each 1 to 4
ESCB-42-42/NV	42,4	42,4	15800	9600	0,925	51,82 €
ESCB-48-42/NV	48,3	42,4	15800	9600	0,925	51,82 €
ESCB-48-48/NV	48,3	48,3	15800	9600	0,925	51,82 €
ESCB-50-42/NV	50,8	42,4	15800	9600	0,925	51,82 €
ESCB-50-48/NV	50,8	48,3	15800	9600	0,925	51,82 €
ESCB-60-42/NV	60,3	42,4	15800	9600	0,925	51,82 €
ESCB-60-48/NV	60,3	48,3	15800	9600	0,925	51,82 €

Dimensions in mm

Support base (tripod)

Plastic


ESSTNV

- ***High stability***
- *Component for conveyor structure*
- *For round tube*
- *Materials:*
  Body: reinforced polyamide
  Screws: stainless steel 304


Accessories


- *Add compatible* **PR** *feet to order* ***(tome 5 p.169)***





Typical application





DISCOUNTS

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	ØDF	Max. load resistance FM (N)	Max. working load. FT (N)	Weight (kg)	Price each 1 to 4
ESST-42/NV	42,4	15800	9600	0,975	49,46 €
ESST-48/NV	48,3	15800	9600	0,975	49,46 €
ESST-50/NV	50,8	15800	9600	0,975	49,46 €
ESST-60/NV	60,3	15800	9600	0,975	49,46 €

Dimensions in mm

Altri prodotti...



Piede fissabile speciale agroalimentare, Stainless steel - 3-A



Cuscinetti a sfere - Accessorio, Spessori metallici centesimali a na...



Ingranaggio dritto Inox, Inox 304L



Ruota, Poliammide



Sfera portante avvitabile miniatura, Miniatura ad avvitare



Sfera portante con flangia per uso alimentare,



Supporto antivibrante a campana, Piastra a base ovale




Rinvio angolare a L, da 1.32 a 4.40 Nm



Distanziatore esagonale, Inox 303



Sistema di guida su binario a V Simple



Cremagliera sezione circolare, Inox -



Cerniera ad avvitare, Aperura 180°

Prodotti correlati



Simple support base (bipod), Plastic



Bipod support base, Plastic



Piede fissabile con snodo - poliammide, Ø 40



Piede fissabile con snodo - poliammide, Ø 50