

Thread inserts are a convenient way of repairing siezed, damaged or hanging threads. It also allows renovate threads in high quality materials.

Thread inserts can be used in varying materials such as light alloys or cast


Advantages

- Quick and easy to install
- Tangs are used during installation and then serve as an anti-rotation mechanism.
- Apart from the insertion tool, no other special tools are required.

Assembly

- Some tapping required
- Refer to technical oages for assembly/disassembly instructions

NEW!



DISCOUNTS

Qty	1+	10+	20+	30+	50+
Disc.	List	-5%	-10%	-15%	On request

Part number	Thread ØD1	Thread ØM	Length L	Assembly drill size Ø	Assembly counterbore size Ø +0,25	Assembly thread	Min thread depth	Removal drill size Ø	Removal thread depth	Price each 1 to 9
FR-M5/SS	M5	M8	8	6,9	8,3	M8	9,5	5,5	4,0	9,83 €
FR-M6/SS	M6	M10x1,25	10	8,8	10,3	M10x1,25	11,5	7,5	4,8	9,56 €
FR-M8/SS	M8	M12x1,25	12	10,8	12,3	M12x1,25	13,5	9,5	4,8	10,09 €
FR-M8x100/SS	M8x1	M12x1,25	12	10,8	12,3	M12x1,25	13,5	9,5	4,8	10,09 €
FR-M10/SS	M10	M14x1,5	14	12,8	14,3	M14x1,5	15,5	11,5	4,8	11,57 €
FR-M10x125/SS	M10x1,25	M14x1,5	14	12,8	14,3	M14x1,5	15,5	11,5	4,8	11,57 €
FR-M12/SS	M12	M16x1,5	16	14,8	16,3	M16x1,5	17,5	13,5	4,8	14,73 €
FR-M12x125/SS	M12x1,25	M16x1,5	16	14,8	16,3	M16x1,5	17,5	13,5	4,8	14,73 €

Altri prodotti...



CHA1056_U20

Cerniera ad avvitare,
Sezione 76x50



RFK28B

Riduttore ipoide inox,
fino a 130 Nm



CHTRP

Riduttore a rinvio
angolare a L o a T,
fino a 9,1 Nm



TBEBASE10

Economic mini-table
with trapezoidal
lead screw, Economica



MF

Deceleratore, Flangia
rettangolare



SVG

Chiusura a leva
regolabile, Corsa da
106,7mm a 121,4mm



CLM

Attacco per forcella,
Corta inox



RPCtcss

Ruota girevole a foro
centrale, Inox -
Poliammide



MSP23

Inserto con piastrina a
incollare
Masterplate®,



MEP

Impugnatura cilindrica
libera, Fissa



LRHSS

Vite trapezoidale a
doppia inclinazione, a
doppia inclinazione - 1



VHTM

Hexagonal headed
bolt Hygienic
Design®, Inox

Prodotti correlati



FR

Inserti filettati, Acciaio



FRtool

Attrezzi per inserti
filettati, Attrezzo di
posa



CHCSS

Vite a testa cava
esagonale CHC, Inox -
A2



BHC

Vite a testa bombata
BHC , Inox A2