

Thread inserts are a convenient way of repairing siezed, damaged or hanging threads. It also allows renovate threads in high quality materials.

Thread inserts can be used in varying materials such as light alloys or cast


Advantages

- Quick and easy to install
- Tangs are used during installation and then serve as an anti-rotation mechanism.
- Apart from the insertion tool, no other special tools are required.

Assembly

- Some tapping required
- Refer to technical oages for assembly/disassembly instructions

NEW!



DISCOUNTS

Qty	1+	10+	20+	30+	50+
Disc.	List	-5%	-10%	-15%	On request

Part number	Thread ØD1	Thread ØM	Length L	Assembly drill size Ø	Assembly counterbore size Ø +0,25	Assembly thread	Min thread depth	Removal drill size Ø	Removal thread depth	Price each 1 to 9
FR-M5/SS	M5	M8	8	6,9	8,3	M8	9,5	5,5	4,0	9,83 €
FR-M6/SS	M6	M10x1,25	10	8,8	10,3	M10x1,25	11,5	7,5	4,8	9,56 €
FR-M8/SS	M8	M12x1,25	12	10,8	12,3	M12x1,25	13,5	9,5	4,8	10,09 €
FR-M8x100/SS	M8x1	M12x1,25	12	10,8	12,3	M12x1,25	13,5	9,5	4,8	10,09 €
FR-M10/SS	M10	M14x1,5	14	12,8	14,3	M14x1,5	15,5	11,5	4,8	11,57 €
FR-M10x125/SS	M10x1,25	M14x1,5	14	12,8	14,3	M14x1,5	15,5	11,5	4,8	11,57 €
FR-M12/SS	M12	M16x1,5	16	14,8	16,3	M16x1,5	17,5	13,5	4,8	14,73 €
FR-M12x125/SS	M12x1,25	M16x1,5	16	14,8	16,3	M16x1,5	17,5	13,5	4,8	14,73 €

Altri prodotti...



PR125

Piede fissabile con snodo - poliammide, Ø 123



GAL_20

Rullo per trasportatore, Polietilene autolubrificato



CLG1

Ingranaggio dritto in plastica stampata , Nylon stampato



PCS_PA6

, 12.7mm (DIN 08B-1)



MHSC

Giunto flessibile a disco semplice, Disco semplice



TB8

Cuscinetto assiale a rulli cilindrici, Acciaio



PSG2

Ingranaggio dritto di precisione, Acciaio 35NCD6 pretrattato



PCS37

Pignone a catena - acciaio, 9.525mm (DIN06B-1)




SDC

Boccole di posizionamento per



H2

Ingranaggio elicoidale ad assi incrociati a



M1

Vite senza fine, Plastica lavorata



PM4

Vite senza fine, Acciaio temprato

Prodotti correlati



FR

Inserti filettati, Acciaio



FRtool

Attrezzi per inserti filettati, Attrezzo di posa



CHCSS

Vite a testa cava esagonale CHC, Inox - A2



BHC

Vite a testa bombata BHC , Inox A2