

- Magnetic strip

- The sensor contains magnetoresistive bridges which read information from the magnetic band which is transmitted to an electronic conversion circuit.
- The P25 magnetic band, which contains a 2.5mm magnetic pole, comprises of

A: A flexible magnetised plasto-ferrite band

B: A metallic strip to provide protection against dirt and any risk of mechanical friction, this is recommended and should be installed by the customer

C: A factory assembled corrosion resistant metal strip to be fixed in place on the machine or in the modular support

- Other lengths available, please ask for details

End-cap


- For an aesthetic finish

Butt jointed modular support



- Material: anodised aluminium

Magnetic ring-shaped sensor


- For measuring the angular displacement (in degrees) of a $\varnothing 14$ or $\varnothing 20$ shaft
- To be used with a multifunction display with external sensor only F7-E
- Sensor 120 steps (pitch 3°)




Ring F7-AM



Magnetic band F7-P25/10-500



Band end-cap (2 pieces)



Modular support F7-SB-500

DISCOUNTS

Qty	1+	3+
Disc	List	On request


Part number	Type	Length (mm)	Shaft diameter $\varnothing A$	Price each 1 to 2
F7-P25/10-500	Magnetic band	500	-	60,29 €
F7-TB	End-cap	-	-	6,67 €
F7-SB-500	Modular support	500	-	78,16 €
F7-AM14	Magnetic ring	-	14	53,59 €
F7-AM20	Magnetic ring	-	20	53,59 €

Dimensions in mm

Altri prodotti...



SH3
Ingranaggio elicoidale ad assi paralleli, Plastica lavorata (delrin)



RPP
Plastra di giunzione per cinghia RPP, RPP5



QN
Cuscinetto a singola corona di rulli cilindrici, Anello esterno libero



RAS
Snodo angolare a 90° DIN71802, Acciaio



BH01
Cuscinetto radiale flangiato, Montaggio : pressione e colla



ZHBRA
Ingranaggio conico in plastica, 1,25:1 2:1 3:1



HBM
Guida su semi-binari, Boccola di regolazione



V3RA_PTR
Volantino a tre razze, Poliammide



PRF-SCREEN-5
Screen support, Support with 5 axes of rotation



PR65C
Half-articulated foot Ø 65, Ø 65



EFSM
Cuscinetto a flangia quadrata Igubal®, Polimero



SLBE
Pistoncino a molla, Anello distanziatore per pistoncino a molla SLB

Prodotti correlati



F7-E
Visualizzatore multifunzione, Con sensore di posizione esterno



F7-P-AM
Visualizzatore multifunzione, Banda magnetica