

- Magnetic strip

- The sensor contains magnetoresistive bridges which read information from the magnetic band which is transmitted to an electronic conversion circuit.
- The P25 magnetic band, which contains a 2.5mm magnetic pole, comprises of

A: A flexible magnetised plasto-ferrite band

B: A metallic strip to provide protection against dirt and any risk of mechanical friction, this is recommended and should be installed by the customer

C: A factory assembled corrosion resistant metal strip to be fixed in place on the machine or in the modular support

- Other lengths available, please ask for details

End-cap


- For an aesthetic finish

Butt jointed modular support



- Material: anodised aluminium

Magnetic ring-shaped sensor


- For measuring the angular displacement (in degrees) of a $\varnothing 14$ or $\varnothing 20$ shaft
- To be used with a multifunction display with external sensor only F7-E
- Sensor 120 steps (pitch 3°)*




Ring F7-AM



Magnetic band F7-P25/10-500



Band end-cap (2 pieces)



Modular support F7-SB-500


DISCOUNTS

Qty	1+	3+
Disc	List	On request

Part number	Type	Length (mm)	Shaft diameter $\varnothing A$	Price each 1 to 2
F7-P25/10-500	Magnetic band	500	-	60,29 €
F7-TB	End-cap	-	-	6,67 €
F7-SB-500	Modular support	500	-	78,16 €
F7-AM14	Magnetic ring	-	14	53,59 €
F7-AM20	Magnetic ring	-	20	53,59 €


Dimensions in mm

Altri prodotti...



LWH

Guida lineare a sfere -
Sfere acciaio, Carello -
da 9320 N a 71300 N




VP

Volantino a 6 lobi,
Duroplast - Acciaio



ACL-PL

Elementi di giunzione,
Piastra di fissaggio -
176x86 mm




BETASS

Copiglia beta, Beta



ZG125

Ingranaggio dritto in
plastica, Plastica
lavorata (delrin)



M1

Coppia ruota e vite
senza fine , Plastica
lavorata (delrin)



PLM-20SC

Magnete cilindrico,
Magnete cilindrico



PRES2HR

Pressa manuale da
banco, Pressione fino
a 200kg




DOMI50

Accessori di
collegamento, Piastra



DOMI80

Accessori di
collegamento, Piatto
girevole



GPLny

Scovolo, nylon



SLHHlok

Bloccaggio a leva, A
leva orizzontale / base
orizzontale

Prodotti correlati



F7-I

Visualizzatore
multifunzione, Con
sensore di posizione
integrato



F7-E

Visualizzatore
multifunzione, Con
sensore di posizione
esterno