

Spring loaded latch

Bra


LRR

Plated steel or chromed brass

- **Night latch**
- Inward/outward opening versions available (A+ B versions)
- Materials : Plated steel or chromed brass

Info.

- Part N° LRR-50-A/LC replaces the old reference LRR-50



DISCOUNTS

Qty.	1+	51+	101+
Disc.	List -10%	On request	


Part number	A	B	C	D	E	F	G	H	J	K	ØS	Material	Weight (g)	Stock*	Price each 1 to 50
Version A															
LRR-50-A/ZN	50	56	1,5	1,2	16	20	34	27	12	12	4	Steel	71	✓	18,57 €
LRR-50-A/LC	50	56	1,5	1,2	16	20	34	27	12	12	4	Brass	75	✓	25,05 €
Version B															
LRR-50-B/ZN	50	56	1,5	1,2	16	20	34	27	12	12	4	Steel	71	✓	18,57 €
LRR-50-B/LC	50	56	1,5	1,2	16	20	34	27	12	12	4	Brass	75	-	39,69 €

*Depending on availability

- Catch for sprung latch LRR
- Materials : Plated steel or chromed brass



INCREASED
STOCK



DISCOUNTS

Qty.	1+	51+	101+
Disc.	List	-10%	On request

Part number	A	B	C	D	G	H	ØS	Material	Weight (g)	Stock*	Price each 1 to 50
LRR-50-GPV/ZN	50	16	1,5	16	34	16	4	Steel	12	✓	2,75 €
LRR-50-GPV/LC	50	16	1,5	16	34	16	4	Brass	13	✓	6,54 €

*Depending on availability

Altri prodotti...



PDD

Pressore a molla
sensore di
rilevamento, Con asta
di comando per int...



PDM_PDV

Detectable plastic
palm grip, by metal
detectors



PFC

Piede fisso,
Livellamento per
piccoli elementi



HTD5M_25

Puleggia dentata di
trasmissione tipo
HTD, HTD5 Alluminio



PO

Maniglia a ponte -
Multi-settore, Foro
liscio



T5courroie

Cinghia di
posizionamento T, T5
Poliuretano armatura
in acciaio



RFK28B

Riduttore ipoide inox,
fino a 130 Nm



PLM-20SC

Magnete cilindrico di
fermo filettato,
Magnete di fermo
maschiato



GDR880

Guida dritta, Serie
880 e 881



ADL_M

Anello di
sollevamento, Inox



RURp

Rotella girevole con
piastra, Poliuretano -



BPL

Sfera portante con
flangia, Leggero

Prodotti correlati



LRR

Chiavistello con perno
prismatico, Gancio



LRRss

Interblocco di
sicurezza, Chiusura a
molla - inox



LRR22

Small dimension latch
with locking system,
Aluminium



LRRRA

Latch with locking
system, Aluminium