
Steel thread inserts

New Ste

FR — For repairing damaged threads

Thread inserts are a convenient way of repairing siezed, damaged or hanging threads. It also allows renovate threads in high quality materials.

Thread inserts can be used in varying materials such as light alloys or cast materials.




Advantages

- *Quick and easy to install*
- *Tangs are used during installation and then serve as an anti-rotation mechanism.*
- ***Apart from the insertion tool, no other special tools are required.***

Assembly

- ***Some tapping required***
- *Refer to technical oages for assembly/disassembly instructions*



DISCOUNTS

Qty	1+	10+	20+	30+	50+
Disc.	List	-5%	-10%	-15%	On request

Part number	Thread ØD1	Thread ØM	Length L	Assembly drill size Ø	Assembly counterbore +0,25	Assembly thread	Min thread depth	Removal drill size Ø	Removal thread depth	Price each 1 to 9
FR-M5	M5	M8	8	6,9	8,3	M8	9,5	5,5	4,0	4,84 €
FR-M6	M6	M10x1,25	10	8,8	10,3	M10x1,25	11,5	7,5	4,8	5,24 €
FR-M8	M8	M12x1,25	12	10,8	12,3	M12x1,25	13,5	9,5	4,8	5,80 €
FR-M8x100	M8x1	M12x1,25	12	10,8	12,3	M12x1,25	13,5	9,5	4,8	5,80 €
FR-M10	M10	M14x1,5	14	12,8	14,3	M14x1,5	15,5	11,5	4,8	7,19 €
FR-M10x125	M10x1,25	M14x1,5	14	12,8	14,3	M14x1,5	15,5	11,5	4,8	7,19 €
FR-M12	M12	M16x1,5	16	14,8	16,3	M16x1,5	17,5	13,5	4,8	9,28 €
FR-M12x125	M12x1,25	M16x1,5	16	14,8	16,3	M16x1,5	17,5	13,5	4,8	9,28 €

Altri prodotti...


GG3

Ingranaggio dritto rettificato, Acciaio trattato


BFM

Dado trapezoidale, Bronzo - 1 filetto


EIM

Cavallotto Inox, Inox


EBH

Dado cieco Hygienic Design®, Con collare


VTHA

Vite magnetica a testa esagonale, Acciaio


NPCR

Morsetto porta fotocellule, Regolabile


LPCM

Leva con impugnatura cilindrica, Duroplast nero, leva in acciaio


PAM_SS

Piede snodato con base lamiera, Ø 30 & 40


DOG258

Motoriduttore DC 12V e 24V DC, da 12 a 15


SUA4_L

Giunzione per catena al metro, Falsa maglia


CSS

Snodo sferico, acciaio/acciaio


M0

Ruota per vite senza fine , Bronzo

Prodotti correlati


FRtool

Attrezzi per inserti filettati, Attrezzo di posa


FRss

Inserti filettati, Inox


INS

Boccola autofilettante acciaio, acciaio


CHC

Vite a testa cava esagonale CHC, Acciaio classe 12.19