

FR For repairing damaged threads

Thread inserts are a convenient way of repairing siezed, damaged or hanging threads. It also allows renovate threads in high quality materials.

Thread inserts can be used in varying materials such as light alloys or cast materials.

Advantages

- Quick and easy to install
- Tangs are used during installation and then serve as an anti-rotation mechanism.
- **Apart from the insertion tool, no other special tools are required.**


Assembly

- **Some tapping required**
- Refer to technical oages for assembly/disassembly instructions



NEW!

Locking tang



DISCOUNTS

Qty	1+	10+	20+	30+	50+
Disc.	List	-5%	-10%	-15%	On request

Part number	Thread ØD1	Thread ØM	Length L	Assembly drill size Ø	Assembly counterbore +0,25	Assembly thread	Min thread depth	Removal drill size Ø	Removal thread depth	Price each 1 to 9
FR-M5	M5	M8	8	6,9	8,3	M8	9,5	5,5	4,0	4,84 €
FR-M6	M6	M10x1,25	10	8,8	10,3	M10x1,25	11,5	7,5	4,8	5,24 €
FR-M8	M8	M12x1,25	12	10,8	12,3	M12x1,25	13,5	9,5	4,8	5,80 €
FR-M8x100	M8x1	M12x1,25	12	10,8	12,3	M12x1,25	13,5	9,5	4,8	5,80 €
FR-M10	M10	M14x1,5	14	12,8	14,3	M14x1,5	15,5	11,5	4,8	7,19 €
FR-M10x125	M10x1,25	M14x1,5	14	12,8	14,3	M14x1,5	15,5	11,5	4,8	7,19 €
FR-M12	M12	M16x1,5	16	14,8	16,3	M16x1,5	17,5	13,5	4,8	9,28 €
FR-M12x125	M12x1,25	M16x1,5	16	14,8	16,3	M16x1,5	17,5	13,5	4,8	9,28 €

Altri prodotti...



PW_PWG05

Vite senza fine di precisione, Acciaio



SVT15

Martinetto a vite - Vite traslante, Vite traslante



GBS2z

Vite a ricircolo di sfere, Dado cilindrico



GAL_25

Rullo per trasportatore, Senza cuscinetti a sfere



GCA

Copiglia a scatto, A scatto



CYS

Anello di arresto interno DIN472, interno DIN 472



MAX26

Motoriduttore DC 12V e 24V DC, da 0,075 a 0,6Nm



CPAS-H

Squadra pieghevole, Per carico pesante



SUA4_L

Giunzione per catena al metro, Falsa maglia - acciaio



VHTM

Hexagonal headed bolt Hygienic Design®, Inox



GSI_A

Molla a gas regolabile inox, Inox



HCA


Grano magnetico con esagono incassato, Acciaio

Prodotti correlati



FRtool

Attrezzi per inserti filettati, Attrezzo di posa



FRss

Inserti filettati, Inox



INS

Boccola autofilettante acciaio, acciaio



CHC

Vite a testa cava esagonale CHC, Acciaio classe 12.19