



- Nut for use with a ballscrew
- Axial backlash: 0.05 mm for screws with 5mm pitch 0.1 mm for screws with 5mm pitch
- Material:  
16 MnCr5 or 100 Cr6



### Accessories

- Please see the **KGS** ballscrew  
The pitch and diameter must be the same as that of the nut)



### DISCOUNTS

Qty	1+	2+	6+	11+
Disc.	List	-7%	-13%	On request

Part number	ØD1g6	ØD2	L1	L3	L4	L5	BxT
GBS-Z-2005-RH	32	3	34	6,75	20	7	5x2
GBS-Z-2505-RH	38	3	34	6,75	20	7	5x2
GBS-Z-3205-RH	45	3	45	7,25	30	7,5	6x2,5
GBS-Z-3210-RH	53	3	60	10	30	15	6x2,5
GBS-Z-4005-RH	53	3	45	7,25	30	7,5	6x2,5
GBS-Z-5010-RH	72	4	82	11	36	23	6x2,5
GBS-Z-6310-RH	85	4	82	11	36	23	6x2,5

Part number	For screw		Load		Weight (kg)	Price each
	Ø	Travel per revolution (mm)	dynamic C (kN)	static Co (kN)		
GBS-Z-2005-RH	20	5	8,00	17,00	0,15	167,73 €
GBS-Z-2505-RH	25	5	9,50	22,40	0,20	191,27 €
GBS-Z-3205-RH	32	5	17,00	49,00	0,30	271,67 €
GBS-Z-3210-RH	32	10	25,70	56,00	0,60	320,19 €
GBS-Z-4005-RH	40	5	19,00	63,50	0,50	342,63 €
GBS-Z-5010-RH	50	10	55,00	153,00	1,10	447,16 €
GBS-Z-6310-RH	63	10	60,00	200,00	1,50	754,68 €

Dimensions in mm

## Altri prodotti...



PC550  
Pignone a catena -  
acciaio, 12.7mm  
(DIN08B-1)



LOQ  
Accessori per porte,  
Fermaporte a scatto



ESCON  
Accessori per  
variatore di velocità  
5A, Kit 4 cavi motore  
DC



OP2  
Indicatore di posizione  
digitale (N. di giri), 3  
cifre



BPFss  
Supporto a flangia  
tonda a carico leggero  
inox, Inox



PITAss  
Pistoncino a molla,  
con maniglia a T



CSS  
Snodo sferico,  
acciaio/acciaio  
autolubrificante



PSG125  
Ingranaggio dritto di  
precisione, Acciaio  
20NCD2 cementato  
temprato



PW\_PWG05  
Ruota di precisione,  
Bronzo



PF60  
Riduttore a ruota e  
vite senza fine, fino a  
118 Nm



M2  
Vite senza fine,  
Acciaio temprato



PRF\_CLIP\_45  
Clip di fissaggio per  
cavi per profili  
alluminio, Per  
canalina di ca...

## Prodotti correlati



KGS  
Vite a ricircolo di sfere  
al metro, Vite a sfere  
rullata, al metro



GBS  
Dado per vite a sfere,  
Dado flangiato