

## NTM<sub>DL</sub>

## Blackened steel finish

### Material

- Screw : steel (class 10.9)
- Tip : Delrin


### Info.

The tip is fitted into the screw.  
These screws are designed to lock or gently hold screws, axles, shafts or other components with a high quality surface finish.



**NEW !**


Delrin tip



### DISCOUNTS

Qty	1+	20+	30+	40+	60+	100+	300+
Disc. Prix	-10%	-15%	-20%	-25%	-45%	On request	

Part number	ØD	ØD1	L	SW	Price each 1 to 19
NTM4-7/DL	M4	2	7	2	2,78 €
NTM4-9/DL	M4	2	9	2	2,78 €
NTM4-11/DL	M4	2	11	2	2,78 €
NTM4-13/DL	M4	2	13	2	2,78 €
NTM4-17/DL	M4	2	17	2	2,78 €
NTM4-31/DL	M4	2	31	2	6,70 €
NTM4-41/DL	M4	2	41	2	6,85 €
NTM5-9/DL	M5	3	9	2,5	2,57 €
NTM5-11/DL	M5	3	11	2,5	2,57 €
NTM5-13/DL	M5	3	13	2,5	2,57 €
NTM5-17/DL	M5	3	17	2,5	2,57 €
NTM5-21/DL	M5	3	21	2,5	2,78 €
NTM5-31/DL	M5	3	31	2,5	7,21 €
NTM5-41/DL	M5	3	41	2,5	7,32 €



Part number	ØD	ØD1	L	SW	Price each 1 to 19
NTM6-11/DL	M6	3,5	11,3	3	2,57 €
NTM6-13/DL	M6	3,5	13,3	3	2,57 €
NTM6-17/DL	M6	3,5	17,3	3	2,78 €
NTM6-21/DL	M6	3,5	21,3	3	2,78 €
NTM6-26/DL	M6	3,5	26,3	3	2,92 €
NTM6-41/DL	M6	3,5	41,3	3	7,37 €
NTM6-51/DL	M6	3,5	51,3	3	7,51 €
NTM6-61/DL	M6	3,5	61,3	3	7,57 €
NTM8-13/DL	M8	5	13,6	4	2,92 €
NTM8-17/DL	M8	5	17,6	4	2,92 €
NTM8-21/DL	M8	5	21,6	4	2,97 €
NTM8-26/DL	M8	5	26,6	4	3,19 €
NTM8-33/DL	M8	5	33,6	4	3,60 €
NTM8-51/DL	M8	5	51,6	4	7,21 €
NTM8-61/DL	M8	5	61,6	4	7,32 €
NTM8-81/DL	M8	5	81,6	4	7,37 €
NTM10-18/DL	M10	6,5	17,9	5	3,49 €
NTM10-22/DL	M10	6,5	21,9	5	3,60 €
NTM10-27/DL	M10	6,5	26,9	5	3,66 €
NTM10-34/DL	M10	6,5	33,9	5	4,22 €
NTM10-42/DL	M10	6,5	41,9	5	4,84 €
NTM10-52/DL	M10	6,5	51,9	5	7,32 €
NTM10-62/DL	M10	6,5	61,9	5	7,42 €
NTM10-82/DL	M10	6,5	81,9	5	7,51 €
NTM12-22/DL	M12	8	22,1	6	4,06 €
NTM12-27/DL	M12	8	27,1	6	4,22 €
NTM12-34/DL	M12	8	34,1	6	4,59 €
NTM12-42/DL	M12	8	42,1	6	5,16 €
NTM12-52/DL	M12	8	52,1	6	5,92 €
NTM12-62/DL	M12	8	62,1	6	7,57 €
NTM12-82/DL	M12	8	82,1	6	7,73 €

## Altri prodotti...



VPSS

Volantino a 6 lobi,  
Duroplast - Inox



SUPTOOL

Attrezzo di montaggio  
per calettatori, Per  
calettatori di  
bloccaggio



SSG0

Ingranaggio dritto  
Inox, Inox 304L



BAG

Anello di bloccaggio in  
acciaio, Acciaio



BWU

Guida lineare di  
precisione, da 1510 N  
a 10500 N



BIM

Pistoncino a molla,  
miniatura



EMS

Volantino zigrinato,  
Zigrinato



COA-COG

Staffa di montaggio  
per molla a gas,  
Staffa di montaggio  
piana per s...



UTKpwrr

Guida lineare  
Utilitrack®, Profilo



MEB

Ingranaggio conico in  
plastica stampata, 1:1



T5-BAR

Barra dentata, T5



EBC

Dado cieco Hygienic  
Design®, Compatto

## Prodotti correlati



NTMbr

Grano punta in  
ottone, punta in  
ottone



NTM

Grano punta in nylon,  
punta in nylon