



Magnetic stud with central hole



PLC

Ferrite

- Cup mounted Ferrite magnet with smooth bored hole
- Working temperature: -50°C to +100°C
- Good corrosion resistance
- Good mechanical resistance



Uses

- Mounting of objects where space is limited or mounting notice boards, protective covers etc
- Positioning of stops or inserts used in moulding machines

-50%**

DISCOUNTS

Qty.	1+	6+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request

Part number	ØD	H	Ød	ØA	F (daN)	Weight (g)	Stock*	Price each 1 to 5
PLC50-10	50	10	8,5	22,0	18	85	✓	8,56 €
PLC63-14	63	14	6,5	24,0	29	197	✓	15,17 €
PLC80-18	80	18	6,5	11,5	54	458	-	29,45 €

*Depending on availability



PLT Magnetic stud with threaded hole

Ferrite

- Cup mounted Ferrite magnet with smooth bored hole
- Working temp.: -50°C to +100°C
- Good corrosion resistance
- Good mechanical resistance

Uses

- Fastening: protective casing, tool machines, support cables...
- Positioning: stops, inserts...
- Gripping: inaccessible places, transport



DISCOUNTS

Qty.	1+	6+	20+	40+	60+
Disc.	List	-15%	-20%	-30%	On request

Part number	ØD	L	H	Ød	ØM	F (daN)	Weight (g)	Stock*	Price each 1 to 5
PLT25-15	25	15	7	8	M4	4,0	22	✓	5,10 €
PLT32-15	32	15	7	8	M4	8,0	32	✓	5,75 €
PLT40-18	40	18	8	10	M5	12,5	60	✓	7,71 €
PLT50-22	50	22	10	12	M6	22,0	110	✓	9,34 €
PLT63-30	63	30	14	15	M8	35,0	240	-	17,46 €
PLT80-34	80	34	18	20	M10	60,0	520	-	30,88 €
PLT100-42	100	42	22	22	M12	90,0	940	-	73,19 €

*Depending on availability

**On price list 2012

Altri prodotti...



PRJUM05

Supporto per boccola Drylin R®, Chiuso - Corto



SHW

Rondella semplice, Acciaio




PSG1HC

Ingran. dritto di precisione trattato skiving, Acciaio 20NCD2 cement...



DSF

Limitatore di coppia a scivolamento, 4 a 2600 Nm




QN

Cuscinetto a singola corona di rulli cilindrici, Anello esterno libero



CHA60

Cerniera, Rettangolare forata o con fori svasati



MRA

Maglia rapida, Acciaio



LVTMFC

Device for controlling limit switches, For mini-actuator LVT



PRF_RR

Elementi di giunzione, Piastra di raccordo



CFF

Testa a snodo femmina DIN



SCE

Serracavo, Acciaio



SLB

Pistoncino a molla, acciaio classe 5.8

Prodotti correlati



VAP

Magnete con foro centrale, Con foro centrale



PLC_PLT

Magnete, Con foro maschiato