



Commercially available tubes are often used to manufacture trolleys, assembly stations, storage bays or workstations. To provide an environment that will not damage the delicate products being handled, these clip-on brushes, with their thousands of sensitive bristles protect against scratches or scuffs that would then require rework or cause expensive rejects. They are designed for 28mm diameter tubes, are available in 3 fibre thicknesses and can easily be installed on transport or storage system before or after assembly. Should the position of a brush need to be changed for example to improve the protection, they are easily removed for re-mounting in an alternative position.

Mounting arrangement



Typical application





Clip-on support brush

For Ø28mm tubes


MGS

- For vertical, inclined or horizontal storage systems or transport applications

Assembly


- Rapid, tool-free assembly
- Works with 28mm diameter tube systems
- Silicon free
- Materials:
 - Fibres: Polyamide 6
 - Body: PVC

NEW!



Advantages

- Easily removed
- Non-slip
- Suitable for all common surfaces (wood, metal, glass)



DISCOUNTS

| | | | | | | |
|------------|-----|------|------|-----|------------|------|
| Qty | 1+ | 20+ | 40+ | 60+ | 80+ | 100+ |
| Disc. List | -5% | -10% | -15% | 20% | On request | |

| Part number | Body length (mm) | FH | Ø fibres | Fibre colors | Fibre texture | Price each 1 to 19 |
|-------------|------------------|----|----------|--------------|---------------|--------------------|
| MGS2800-K10 | 40 | 5 | 0,10 | black | smooth | 3,95 € |
| MGS2800-K20 | 40 | 5 | 0,20 | blue | smooth | 3,95 € |
| MGS2800-K30 | 40 | 5 | 0,30 | red | smooth | 3,95 € |

Dimensions in mm

Altri prodotti...



SCH

Attrezzo di bloccaggio, A tirante orizzontale - inox



GDR880

Guida dritta, Serie 880 e 881



CHMR90

Riduttore a ruota e vite senza fine, fino a 540 Nm



AT5_16

Puleggia dentata, AT5 alluminio



ZG4

Ingranaggio dritto, Plastica lavorata (delrin)



HBM

Guida su semi-binari, Boccola di regolazione



PRES

Accessori per pressa PRES-3HR e PRES-4HR, Coppia di dadi per scanalatura a



SDA

Pistoncino a molla - Supporto, fissaggio parallelo alla serratura



CLA

Maniglia a ripresa Hygienic Usit®, Inox



RPCtcss

Ruota girevole a foro centrale, Acciaio - Poliammide - a doppio



SERB

Interblocco di sicurezza, Chiave universale per



HTD8M-BAR

Barra dentata per cinghia RPP, HTD8

Prodotti correlati