

Material

- Screw : steel (class 10.9)
- Tip : brass


Info.

The tip is fitted into the screw.
These screws are designed to lock or gently hold screws, axles, shafts or other components with a high quality surface finish.



NEW!


Brass tip



DISCOUNTS


Qty	1+	20+	30+	40+	60+	100+	300+
Disc.	Prix	-10%	-15%	-20%	-25%	-45%	On request

Part number	ØD	ØD1	L	SW	Price each. 1 to 19
NTM4-6/BR	M4	2,5	6,5	2	5,47 €
NTM4-10/BR	M4	2,5	10,5	2	5,47 €
NTM4-16/BR	M4	2,5	16,5	2	5,65 €
NTM4-30/BR	M4	2,5	30,5	2	7,60 €
NTM4-40/BR	M4	2,5	40,5	2	7,74 €
NTM5-8/BR	M5	3	8,5	2,5	4,91 €
NTM5-12/BR	M5	3	12,5	2,5	4,91 €
NTM5-20/BR	M5	3	20,5	2,5	5,15 €
NTM5-30/BR	M5	3	30,5	2,5	7,74 €
NTM5-40/BR	M5	3	40,5	2,5	7,84 €



Part number	ØD	ØD1	L	SW	Price each. 1 to 19
NTM6-11/BR	M6	4,0	11,5	3	4,91 €
NTM6-17/BR	M6	4,0	17,5	3	4,91 €
NTM6-26/BR	M6	4,0	26,5	3	5,15 €
NTM6-41/BR	M6	4,0	41,5	3	7,89 €
NTM6-51/BR	M6	4,0	51,5	3	8,02 €
NTM6-61/BR	M6	4,0	61,5	3	8,06 €
NTM8-12/BR	M8	5,5	12,0	4	5,10 €
NTM8-22/BR	M8	5,5	22,0	4	5,10 €
NTM8-32/BR	M8	5,5	32,0	4	5,24 €
NTM8-52/BR	M8	5,5	52,0	4	8,17 €
NTM8-62/BR	M8	5,5	62,0	4	8,30 €
NTM8-82/BR	M8	5,5	82,0	4	8,35 €
NTM10-14/BR	M10	7,0	14,0	5	5,80 €
NTM10-18/BR	M10	7,0	18,0	5	5,80 €
NTM10-27/BR	M10	7,0	27,0	5	5,97 €
NTM10-37/BR	M10	7,0	37,0	5	6,30 €
NTM10-52/BR	M10	7,0	52,0	5	8,30 €
NTM10-62/BR	M10	7,0	62,0	5	8,44 €
NTM10-82/BR	M10	7,0	82,0	5	8,58 €
NTM12-18/BR	M12	8,5	18,5	6	6,44 €
NTM12-22/BR	M12	8,5	22,5	6	6,44 €
NTM12-32/BR	M12	8,5	32,5	6	6,96 €
NTM12-42/BR	M12	8,5	42,5	6	7,50 €
NTM12-52/BR	M12	8,5	52,5	6	8,44 €
NTM12-62/BR	M12	8,5	62,5	6	8,62 €
NTM12-82/BR	M12	8,5	82,5	6	8,86 €

Altri prodotti...



M1

Vite senza fine,
Plastica lavorata
(delrin)



EKN

Giunto a soffietto
Gerwah®, da 0.5 a
12Nm



DOMI50

Accessori di
collegamento, Piastra



BTC20_10

Tappo per tubo
rettangolare,
Standard



MSP23

Inserto con piastrina a
incollare
Masterplate®,
Cilindrico Ø23 con...



EKONSL

Piedino antivibrante
conico silicone,
Fissaggio femmina



NDS20

Connettore di
serraggio, Parallela



DOMI50

Accessori di
collegamento, Piatto
girevole



FF40

Riduttore ad alberi
paralleli, da 59 a 210



DOMI30

Kit di raccordo, Kit di
raccordo XZ



BFDdII

Boccola di fermo per
perno ad innesto,



GTCS5

Rullo tendicinghia, Per
ambienti aggressivi

Prodotti correlati



NTMdl

Grano punta in delrin,
punta in delrin



NTM

Grano punta in nylon,
punta in nylon