

# Idler sprocket for plate chain



## PR820

## For chain ranges 820 and 815

- For use with CAP820 and CAP815 plate chains

- Materials:

Reinforced polyamide

Stainless steel screws


- Operating temp.: -10°C to +120°C

- For dimensions and bore tolerances, please refer to technical pages



### Advantage

- Two part design facilitates easy assembly

**Easy assembly**



Two part design



### DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	No. of teeth	ØDE	ØDP	Bore ØA	Weight (kg)	Price each 1 to 4
PR820-21-25	21	129	129,26	25	0,4	28,49 €
PR820-21-30	21	129	129,26	30	0,4	28,49 €
PR820-21-35	21	129	129,26	35	0,4	28,49 €
PR820-21-40	21	129	129,26	40	0,4	28,49 €
PR820-21-45	21	129	129,26	45	0,4	28,49 €
PR820-23-25	23	141	141,22	25	0,5	30,09 €
PR820-23-30	23	141	141,22	30	0,5	30,09 €
PR820-23-35	23	141	141,22	35	0,5	30,09 €
PR820-23-40	23	141	141,22	40	0,5	30,09 €
PR820-23-45	23	141	141,22	45	0,5	30,09 €
PR820-25-25	25	153	153,20	25	0,5	30,39 €
PR820-25-30	25	153	153,20	30	0,5	30,39 €
PR820-25-35	25	153	153,20	35	0,5	30,39 €
PR820-25-40	25	153	153,20	40	0,5	30,39 €
PR820-25-45	25	153	153,20	45	0,5	30,39 €

Dimensions in mm

## Altri prodotti...



HRV

Sistema di guida su binario a V Simple Select®, Binario con carrello



ACLEPP

Angolare, 8 fori



DOMI\_MD

Tavola rotante di regolazione Domino, 55/1



INS150

Inserto auto-maschiante a passo grosso, Con colletto - filetto largo



MDB\_MTB

Ingranaggio conico in plastica stampata , 3:1




MBrondelle

Cuscinetti a sfere - Accessorio, Rondella di arresto MB



Q6

Cuscinetto radiale a sfere, Acciaio



PDR-RD

Piede con ruota integrata, Ruota disassata



PCATherm

Pull handle, Thermoplastic




E60

Riduttore a rinvio angolare, da 4.50 a



HW\_HT

Guida su semi-binari, Binario



LAT4

Attuatore lineare a motore 4A, 4 ampere

## Prodotti correlati



CAP820

Catena a tapparella dritta, Stretta serie 820



CAP815

Catena a tapparella dritta, Stretta serie 815



DBL820

Rotella per catena, Serie 820 e 815



PT820

Pignone di trazione, Serie 820 e 815