

# Idler sprocket for plate chain



## PR820

## For chain ranges 820 and 815

- For use with CAP820 and CAP815 plate chains

- Materials:

Reinforced polyamide

Stainless steel screws


- Operating temp.: -10°C to +120°C

- For dimensions and bore tolerances, please refer to technical pages



### Advantage

- Two part design facilitates easy assembly

**Easy assembly**



Two part design




### DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	No. of teeth	ØDE	ØDP	Bore ØA	Weight (kg)	Price each 1 to 4
PR820-21-25	21	129	129,26	25	0,4	28,49 €
PR820-21-30	21	129	129,26	30	0,4	28,49 €
PR820-21-35	21	129	129,26	35	0,4	28,49 €
PR820-21-40	21	129	129,26	40	0,4	28,49 €
PR820-21-45	21	129	129,26	45	0,4	28,49 €
PR820-23-25	23	141	141,22	25	0,5	30,09 €
PR820-23-30	23	141	141,22	30	0,5	30,09 €
PR820-23-35	23	141	141,22	35	0,5	30,09 €
PR820-23-40	23	141	141,22	40	0,5	30,09 €
PR820-23-45	23	141	141,22	45	0,5	30,09 €
PR820-25-25	25	153	153,20	25	0,5	30,39 €
PR820-25-30	25	153	153,20	30	0,5	30,39 €
PR820-25-35	25	153	153,20	35	0,5	30,39 €
PR820-25-40	25	153	153,20	40	0,5	30,39 €
PR820-25-45	25	153	153,20	45	0,5	30,39 €

Dimensions in mm

## Altri prodotti...



PRFbou

Sistema di chiusura,  
Pulsante apriporta di  
emergenza



CHAGC-AL

Cerniera ad avvitare,  
Sfilabile



BLH40

Rinvio angolare a L,  
da 3 a 10.30 Nm




J51

Riduttore coassiale a  
treni paralleli, da 0.13  
a 0.49 - a treni para...



ACLERP

Rulliera, Con guida  
laterale



PTBss

Bullone a occhiello  
inox, Inox



PRF\_GAL

Rotella per profilo  
alluminio, Rotella  
liscia



ACLCHARJ

Cerniera ad avvitare,  
Adjusts in 2 directions




AZY\_SS

Antivibrante elastico  
cilindrico inox, Inox



SSG2\_304L

Ingranaggio dritto  
Inox, Inox 304L



SHWbr

Rondella semplice -  
DIN125, Ottone



HW\_HT

Guida su semi-binari,  
Ruota

## Prodotti correlati



CAP820

Catena a tapparella  
dritta, Stretta serie  
820



CAP815

Catena a tapparella  
dritta, Stretta serie  
815



DBL820

Rotella per catena,  
Serie 820 e 815



PT820

Pignone di trazione,  
Serie 820 e 815