

Shaft support for aluminium profile Stock

PRFPSA **MiniTec** For attaching a guidance shaft to a profile Z12

- Support profile for linear guide shafts

- Materials:


Profile: anodised aluminium E6/V1

Steel shaft: Cf53 hardened (62 +/-2 HRC) Stainless steel

shaft: hardened stainless steel X90CrMoV18 (57 +/-2 HRC)

Shaft end stop: grey power coated aluminium

(Fixing kit supplied)




Assembly


- Insert the shaft support profile into the profile slot
- Secure with M5x10 grub screws
- Insert the shaft into the support profile with the aid of a plastic mallet if necessary

Accessories

- Roller PRF-GAL-12
- Shaft end stop PRF-12-AA



PRF-12-PSA



PRF-12-AA

DISCOUNTS

Qty.	1+	50+	100+
Disc.	List -5%	On request	

DISCOUNTS SHAFTS Z

Qty.	1+	6+	20+	40+	60+	100+
Disc.	List -10%	List -15%	List -20%	List -25%	On request	

Part number	For profile	Material	Length	Weight (kg/m)	Stock*	Price each
Shaft support profile						
PRF-12-PSA	all types	-	3000	0,36	✓	22,85 €
Linear guidance shaft						
Z-12-3000A		steel	3000	0,89	-	46,08 €
Z-12-3000B		stainless steel	3000	0,89	-	148,34 €
Shaft end stop						
PRF-12-AA		-	-	0,03	-	6,20 €

*Depending on availability - Dimensions in mm

Altri prodotti...



G2
Ingranaggio dritto
acciaio, Acciaio
20NCD2



SCA_SS
Serracavo, Inox



MEP
Impugnatura cilindrica
libera, Fissa



AFA
Perno di fissaggio, con
anello



GMK17_RG
Morsetto di giunzione,
Per guida prodotto
laterale



BOX-WM
Rondella semplice -
DIN125, Valigetta di
rondelle acciaio



M0
Vite senza fine ,
Acciaio non temprato



BLHM60
Rinvio angolare, fino a
70 Nm



PGR
Impugnatura cilindrica
libera retraibile,



ABL100005
Spazzola antistatica,
Standard



BOX-TOR-MAX
Valigetta di
guarnizioni toriche in




LRR
Chiavistello con perno
prismatico, Gancio

Prodotti correlati



PRF_GAL
Rotella per profilo
alluminio, Rotella
cava $\varnothing 12$



PRF_PSA
Rotella per profilo
alluminio, per
bloccaggio albero