

Shaft support for aluminium profile Stock

PRFPSA **MiniTec** For attaching a guidance shaft to a profile Z12

- Support profile for linear guide shafts

- Materials:


Profile: anodised aluminium E6/V1

Steel shaft: Cf53 hardened (62 +/-2 HRC) Stainless steel

shaft: hardened stainless steel X90CrMoV18 (57 +/-2 HRC)

Shaft end stop: grey power coated aluminium

(Fixing kit supplied)




Assembly


- Insert the shaft support profile into the profile slot
- Secure with M5x10 grub screws
- Insert the shaft into the support profile with the aid of a plastic mallet if necessary

Accessories

- Roller PRF-GAL-12
- Shaft end stop PRF-12-AA



PRF-12-PSA



PRF-12-AA

DISCOUNTS

| | | | |
|-------|----------|------------|------|
| Qty. | 1+ | 50+ | 100+ |
| Disc. | List -5% | On request | |

DISCOUNTS SHAFTS Z

| | | | | | | |
|-------|-----------|------|------|------|------------|------|
| Qty. | 1+ | 6+ | 20+ | 40+ | 60+ | 100+ |
| Disc. | List -10% | -15% | -20% | -25% | On request | |

| Part number | For profile | Material | Length | Weight (kg/m) | Stock* | Price each |
|------------------------------|-------------|-----------------|--------|---------------|--------|------------|
| Shaft support profile | | | | | | |
| PRF-12-PSA | all types | - | 3000 | 0,36 | ✓ | 22,85 € |
| Linear guidance shaft | | | | | | |
| Z-12-3000A | | steel | 3000 | 0,89 | - | 46,08 € |
| Z-12-3000B | | stainless steel | 3000 | 0,89 | - | 148,34 € |
| Shaft end stop | | | | | | |
| PRF-12-AA | | - | - | 0,03 | - | 6,20 € |

*Depending on availability - Dimensions in mm

Altri prodotti...



HTD8M_50
Puleggia dentata di trasmissione tipo HTD, HTD8 Acciaio




ZG2
Ingranaggio dritto in plastica, Plastica lavorata (delrin)



NSP
Morsetto base a 90°, Montaggio e regolazione rapidi



DOMI50
Accessori di collegamento, Piastra



PRF_JL4
Panel accessories, Guarnizione - Ø 4mm



KB_OP
Manicotto a sfere di precisione, Di precisione - acciaio



VPRA_M
Volantino con impugnatura, Plastica termoidurente - Mozzo:acciaio z...



BTE
Tenditore automatico universale, Per applicazioni correnti



GSI
Molla a gas inox, Inox



PR40
Piede fissabile con snodo - poliammide, Ø 50




BS3
Panamech, Multi-Beam inox, Inox - con vite a pressione



VLBG
Anello di sollevamento, Girevole

Prodotti correlati



PRF_PSA
Rotella per profilo alluminio, Supporto d'albero



PRF_PSA
Rotella per profilo alluminio, Albero per guida